

10ft (3m) Computer Power Cord, Right Angle NEMA 5-15P to C13, 10A 125V, 18AWG, Black Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable - UL Listed

Produkt-ID: PXTR10110



This NEMA 5-15P to C13 power cord features a right-angled plug, which positions the connector in such a way that it does not block other available outlets. The cable is especially useful when plugging into a dual AC wall outlet as it frees up the second outlet for another power cord.

The high-quality computer power cord is designed to provide a durable, long-lasting connection to your peripheral devices. It makes a suitable replacement for worn out or missing computer, monitor or printer power cords.

The PXTR10110 is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Save space on a two outlet AC wall outlet
- Plug your monitor, computer, or printer into a grounded power outlet
- Dependable replacement or spare computer power cord

Merkmale

- **AC POWER CORD:** This 10ft (3m) 18AWG flexible computer power cable with Right-Angle NEMA 5-15P and IEC 60320 C13 connectors is suitable for workstation/home office use | Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | 3 Conductor Power Cable made from 100% Copper Wire | Fire Rating: VW-1
- **SPECS:** 10ft (3m) Power Cable | Right-Angle NEMA 5-15P to IEC 60320 C13 | 18AWG | 125V 10A (Max) | Jacket Rating: SJT | Jacket Material: PVC | Color: Black | Temperature Range: 37°F to 140°F (3 to 60) | Cable Outer Diameter: 0.3in (7.8mm)
- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets | IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more | Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance | This C13 power cord is available in other lengths

Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 3

Kabeltyp SJT

Steckverbinder

Steckverbinder A 1 - NEMA 5-15 Strom (Nordamerika)
1 - IEC 60320 C13 Strom

Spezielle Hinweise/Anforderungen

Hinweis UL Listed

Strom

Eingangsspannung 125 AC

Eingangsstrom 10 A

Physische Eigenschaften

Farbe	Schwarz
Steckverbinderart	Right Angle to Straight
Drahtstärke	18 AWG
Kabellänge	10.0 ft [3.0 m]
Produktlänge	10.0 ft [3.0 m]
Produktbreite	1.1 in [2.7 cm]
Produkthöhe	1.6 in [4.1 cm]
Produktgewicht	10.6 oz [300.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	10.0 in [25.4 cm]
Paketbreite	3.9 in [10.0 cm]
Pakethöhe	1.7 in [4.3 cm]
Versandgewicht (Verpackung)	10.7 oz [302.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - NEMA 5-15P to C13 power cord
--------------------	----------------------------------

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.