

10ft (3m) Computer Power Cord, Right Angle NEMA 5-15P to C13, 10A 125V, 18AWG, Black
Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable -
UL Listed

Product ID: PXTR10110



This NEMA 5-15P to C13 power cord features a right-angled plug, which positions the connector in such a way that it does not block other available outlets. The cable is especially useful when plugging into a dual AC wall outlet as it frees up the second outlet for another power cord.

The high-quality computer power cord is designed to provide a durable, long-lasting connection to your peripheral devices. It makes a suitable replacement for worn out or missing computer, monitor or printer power cords.

The PXTR10110 is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Save space on a two outlet AC wall outlet
- Plug your monitor, computer, or printer into a grounded power outlet
- Dependable replacement or spare computer power cord

Features

- **AC POWER CORD:** This 10ft (3m) 18AWG flexible computer power cable with Right-Angle NEMA 5-15P and IEC 60320 C13 connectors is suitable for workstation/home office use. Rated to carry 125V at 10A.
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817). Fully molded strain relief connectors for durability. 3 Conductor Power Cable made from 100% Copper Wire. Fire Rating: VW-1.
- **SPECS:** 10ft (3m) Power Cable. Right-Angle NEMA 5-15P to IEC 60320 C13. 18AWG. 125V 10A (Max). Jacket Rating: SJT. Jacket Material: PVC. Color: Black. Temperature Range: 37F to 140F (3 to 60). Cable Outer Diameter: 0.3in (7.8mm).
- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets. IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more. Replacement PC power supply cable/cord.
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance. This C13 power cord is available in other lengths.

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Type	SJT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
	1 - IEC 60320 C13 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	10 A

Physical Characteristics

Color	Black
Connector Style	Right Angle to Straight
Wire Gauge	18 AWG
Cable Length	10.0 ft [3.0 m]

Product Length	10.0 ft [3.0 m]
Product Width	1.1 in [2.7 cm]
Product Height	1.6 in [4.1 cm]
Weight of Product	10.6 oz [300.0 g]

Packaging Information

Package Quantity	1
Package Length	10.0 in [25.4 cm]
Package Width	3.9 in [10.0 cm]
Package Height	1.7 in [4.3 cm]
Shipping (Package) Weight	10.7 oz [302.0 g]

What's in the Box

Included in Package	1 - NEMA 5-15P to C13 power cord
---------------------	----------------------------------

****Product appearance and specifications are subject to change without notice.***