

## Power Cord - Right-Angle NEMA 5-15P to C13 - 3 ft.

Product ID: PXTR1013



This NEMA 5-15P to C13 power cord features a right-angled plug, which positions the connector in a way that doesn't block other available outlets. The cable is especially useful when plugging into a dual AC wall outlet, as it frees up the second outlet for another power cord.

This high-quality computer power cord is designed to provide a durable, long-lasting connection to your peripheral devices. It makes a suitable replacement for worn out or missing computer, monitor or printer power cords.

The PXTR1013 is backed by a StarTech.com lifetime warranty for guaranteed reliability.

### Certifications, Reports and Compatibility



### Applications

- Save space on a multi-receptacle AC wall outlet or power strip
- Plug your monitor, computer, or printer into a grounded power outlet
- Dependable replacement or spare computer power cord

### Features

- Right-angle plug positions the connector to prevent blocking available outlets
- Rated to carry 125V at 10A
- Guaranteed reliability

---

Hardware

Warranty

Lifetime

	Number of Conductors	3
	Cable Type	SJT
<b>Connector(s)</b>	Connector A	NEMA 5-15 Power (North America)
	Connector A	IEC 60320 C13 Power
<b>Special Notes / Requirements</b>	Note	UL Listed
<b>Power</b>	Input Voltage	125 AC
	Input Current	10 A
<b>Physical Characteristics</b>	Color	Black
	Connector Style	Right Angle to Straight
	Wire Gauge	18 AWG
	Cable Length	36.0 in [9.1 cm]
	Product Length	36.0 in [9.1 cm]
	Product Width	1.1 in [27.000 mm]
	Product Height	1.5 in [37.000 mm]
	Weight of Product	4.3 oz [122.000 g]
<b>Packaging Information</b>	Package Length	11.6 in [2.9 cm]
	Package Width	5.7 in [1.4 cm]
	Package Height	1.2 in [30.000 mm]
	Shipping (Package) Weight	4.5 oz [128.000 g]
<b>What's in the Box</b>	Included in Package	NEMA 5-15P to C13 power cord

*\*Product appearance and specifications are subject to change without notice.*

