

MSA Uncoded Compatible 3m 40G QSFP+ to QSFP+ Direct Attach Breakout Cable Twinax - 40 GbE QSFP+ Copper DAC 40 Gbps Low Power Passive Transceiver Module DAC

**Product ID:** QSFP40GPC3M



The QSFP40GPC3M is an MSA compliant direct-attach copper QSFP+ cable that's designed, programmed and tested to work in 40G network deployments. It delivers dependable 40 GbE connectivity over copper cabling, which is a cost-effective alternative to fiber-optic cable setups.

This passive Twinax cable supports 40 Gigabit Ethernet applications connected through QSFP+ (Mini-GBIC) ports. The cable is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

At 3 meters long and designed for high-speed performance, this copper QSFP+ cable is ideal for medium-distance applications such as across-rack network switch or server connections.

All StarTech.com SFP & SFP+ cables are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of direct-attach SFP Cables and SFP modules, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility

### Applications

- Use in 40Gb Ethernet network applications
- Point-to-point in-rack and across-rack server or network switch connections

### Features

- MSA UNCODED QSFP+ CABLE (DAC): 40G direct attach cable works with MSA compliant switches the accept uncoded transceivers and modules

- **TECHNICAL SPECS:** 3m (9.84ft) 40 Gbps Passive Twinax (Copper) 2x QSFP+ Pluggable Connector 100 Ohm Impedance 30 AWG Wire Gauge PVC Cable Jacket Hot swappable MSA Compliant
- **DESIGNED FOR SERVER ROOMS:** DAC is a cost-effective copper alternative to fiber cable inside & between racks. Factory termination means high performance & reliability with less maintenance.
- **OUTSTANDING SUPPORT:** Backed by StarTech.com for the life of the cable itself, not your equipment; our cables won't void your OEM support and with access to our Tech Advisors 5/24
- Hot-swappable
- **WORKS WITH MSA COMPLIANT SWITCHES:** Low power 40 GbE DAC also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules and transceivers

---

#### Hardware

Warranty	Lifetime
Compatible Brand	MSA Compliant
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	Passive Copper Cable

---

#### Performance

Maximum Data Transfer Rate	40Gbps
Impedance	100 Ohm
Compatible Networks	40 Gbps
Power Consumption (In Watts)	< 0.1 W (per end)

---

#### Connector(s)

Connector A	QSFP+
Connector B	QSFP+

---

#### Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-40C to 80C (-40F to 158F)

---

#### Physical Characteristics

Product Length	9.8 ft [3.0 m]
----------------	----------------



Product Width 0.7 in [18.0 mm]

Product Height 0.3 in [8.0 mm]

Weight of Product 8.9 oz [252.0 g]

---

**Packaging Information**

Package Length 12.8 in [32.5 cm]

Package Width 9.8 in [25.0 cm]

Package Height 1.0 in [25.0 mm]

Shipping (Package) Weight 9.5 oz [268.0 g]

---

**What's in the Box**

Included in Package QSFP+ cable

---

*\*Product appearance and specifications are subject to change without notice.*

