

StarTech.com AOC Breakout Cable for Cisco QSFP-4X10G-AOC5M - 5m/16.4ft 40G 1x QSFP+ to 4x SFP+ AOC Cable - 40GbE QSFP+ Active Optical Fiber - 40Gbps QSFP Plus/Transceiver Module Breakout Cable - C9300 C3850 (QSFP4X10GAO5)

Product ID: QSFP4X10GAO5



The QSFP4X10GAO5 is a Cisco QSFP-4X10G-AOC5M compatible optical quad small form-factor pluggable (QSFP+) breakout cable that is designed, programmed and tested to work with Cisco brand compatible servers or routers and complies with MSA industry standards. Connecting a single QSFP+ port (40 GbE) to four 10G SFP+ ports, this active optical breakout cable is fully hot-pluggable which makes upgrades and replacements seamless by minimizing network disruptions.

The fiber QSFP+ cable is lighter and more flexible than QSFP+ direct-attach cables, making it ideal for installation in tight spaces and over longer distances. It is designed for high-speed interconnects and is great for point-to-point across-rack network switch or server connections, for up to four 10G SFP+ devices.

All StarTech.com QSFP & QSFP+ cables are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of direct-attach SFP Cables and SFP modules, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility

Applications

- Point-to-point in-rack and across-rack server or network switch connections, for up to four devices
- Use in 40Gb/10Gb mixed Ethernet network applications

Features

- TECHNICAL SPECS: 5m (16.4ft) Active Optical Cable 40Gbps Active Optical Fiber 1x QSFP+ to 4x SFP+ Pluggable Connector PVC Cable Jacket Hot swappable MSA Compliant
- DESIGNED FOR SERVER ROOMS: 40GbE AOC is a convenient alternative to transceivers inside and between racks. Factory termination means high performance & reliability, with less maintenance.

- **OUTSTANDING SUPPORT:** Backed by StarTech.com for the life of the cable itself, not your equipment; our cables won't void your OEM warranty and with access to our Tech Advisors 5/24
- **WORKS WITH MSA COMPLIANT SWITCHES:** Low power 40GbE DAC also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules and transceivers
- **100% CISCO QSFP-4X10G-AOC5M COMPATIBLE QSFP+ BREAKOUT DAC:** Works with Cisco switches like C9300, C3850, C9300, C9500, C3650 and others

Hardware	Warranty	Lifetime
	Compatible Brand	Cisco
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Type	Active Optical Cable
Performance	Maximum Data Transfer Rate	40Gbps for QSFP+ / 10Gbps for SFP+
	Compatible Networks	40 Gbps
	Power Consumption (In Watts)	< 1.5 W (per end)
Connector(s)	Connector A	QSFP+
	Connector B	SFP+
Environmental	Operating Temperature	0C to 70C (32F to 158F)
	Storage Temperature	-40C to 80C (-40F to 158F)
Physical Characteristics	Product Length	16.4 ft [5.0 m]
	Product Width	0.6 in [14.000 mm]
	Product Height	0.5 in [12.000 mm]
	Weight of Product	8.4 oz [238.000 g]
Packaging Information	Package Length	12.6 in [3.2 cm]
	Package Width	9.4 in [2.4 cm]
	Package Height	0.8 in [20.000 mm]
	Shipping (Package) Weight	9.2 oz [262.000 g]
What's in the Box	Included in Package	QSFP+ to 4x SFP+ cable

**Product appearance and specifications are subject to change without notice.*