

Cisco QSFP-H40G-ACU10M Compatible 10m 40G QSFP+ to QSFP+ Direct Attach Cable Twinax - 40GbE QSFP+ Copper DAC 40 Gbps Low Power Active Transceiver Module DAC Firepower ASR1000 ASR9000

Product ID: QSFPH40GAC10



This 40G QSFP+ cable delivers what you need most in your network connections: reliable performance. It's built to MSA specifications and fully tested to ensure seamless compatibility.

The active twinaxial cable is a fully hot-pluggable solution, supporting 40 Gigabit Ethernet applications connected through QSFP+ (Quad Small Form-Factor Pluggable) ports.

Designed for high-speed interconnects, this cable is intended for medium-distance applications such as across rack network switch or server connections.

Backed by a StarTech.com lifetime warranty, the QSFPH40GAC10 is a reliable replacement cable for the Cisco QSFP-H40G-ACU10M.

## Certifications, Reports and Compatibility



## Applications

- Use in 40Gb Ethernet network applications
- Point-to-point across-rack server or network switch connections

## Features

- 100% CISCO QSFP-H40G-ACU10M COMPATIBLE: Works with Cisco switches like Firepower, ASR1000, ASR9000, C9300, C3650 and others

- TECHNICAL SPECS: 10m (32.8ft) 40 Gbps Active Twinax (Copper) 2x QSFP+ Pluggable Connector 100 Ohm Impedance 24 AWG Wire Gauge PVC Cable Jacket Hot swappable MSA Compliant
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in Cisco routers and switches
- OUTSTANDING SUPPORT: Backed by StarTech.com for the life of the cable itself, not your equipment; our cables won't void your OEM support and with access to our Tech Advisors 5/24.
- WORKS WITH MSA COMPLIANT SWITCHES: Low power 40GbE DAC also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules and transceivers
- Hot-swappable

<b>Hardware</b>	Warranty	Lifetime
	Compatible Brand	Cisco
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Type	Active Copper Cable
<b>Performance</b>	Maximum Data Transfer Rate	40Gbps 100 Ohm
	Impedance	40 Gbps
	Compatible Networks	
<b>Connector(s)</b>	Connector A	QSFP+
	Connector B	QSFP+
<b>Environmental</b>	Operating Temperature	0C to 70C (32F to 158F)
	Storage Temperature	-40C to 80C (-40F to 158F)
<b>Physical Characteristics</b>	Product Length	32.8 ft [10.0 m]
	Product Width	0.6 in [14.000 mm]
	Product Height	0.5 in [12.000 mm]
	Weight of Product	18.4 oz [520.000 g]
<b>Packaging Information</b>	Package Length	10.6 in [2.7 cm]
	Package Width	9.8 in [2.5 cm]
	Package Height	1.0 in [25.000 mm]
	Shipping (Package) Weight	20.1 oz [570.000 g]
<b>What's in the Box</b>	Included in Package	QSFP+ cable

*\*Product appearance and specifications are subject to change without notice.*