

IP67 Certified 2T2R 2.4GHz Outdoor Wireless-N Access Point - PoE-Powered 300 Mbps
802.11b/g/n WiFi AP

Product ID: R300WN22ODE



The R300WN22ODE Outdoor Wireless Access Point lets you add 2.4GHz Wireless-N network coverage to an outdoor area, through a ruggedized industrial access point.

This outdoor access point features an IP67 certified, die-cast metal enclosure with heavy-duty cable grommets so it can withstand the outdoor elements and offers pole and wall-mounting options. Plus, the PoE-powered AP includes a passive Power-over-Ethernet injector, enabling you to install it in locations where a typical power outlet is unavailable. PoE pass-through via the secondary LAN port lets you connect data and power to a PoE-capable device near the access point.

For optimal wireless coverage, the AP broadcasts a signal through a high-powered 800mW internal 10dBi 2T2R antenna, with 802.11b/g/n compatibility to easily connect most wireless devices new or old.

The device offers support for several different operating modes (AP, WDS and WISP), which help you to create a wireless network from a wired connection, bridge multiple APs together or extend the range of an existing wireless network. The AP supports Wireless-N data rates up to 300Mbps with security through WEP, WPA, or WPA2 authentication, all configurable through an easy-to-use web-based utility.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Create an outdoor Wireless-N access point from an existing wired or wireless connection to eliminate network dead spots and allow wireless devices to connect across large open spaces
- Use WDS (Wireless Distribution System) to mesh multiple Access Points together

- Connect smartphones, tablets or laptops to a Wireless B/G/N access point
- Use the secondary LAN port to deploy remote PoE-Powered devices such as switches or IP cameras

Features

- IEEE 802.11b/g/n (Wireless-N) compliant with speeds up to 300 Mbps @ 2.4GHz
- Metal, IP67 certified pole and wall-mountable housing
- PoE-powered access point with included PoE injector and PoE pass-through
- Supports AP, WDS and WISP operating modes
- 800mW internal 10dBi 2T2R antenna
- Supports WEP, WPA and WPA2 security with TKIP/AES encryption
- Integrated MAC address control and QoS support
- Built-in configuration utility (web-based)
- +/-15kV air and +/-8kV contact ESD (Electrostatic Discharge) Protection

Hardware

Warranty	2 Years
Interface	Wireless Ethernet
Antenna Configuration	2x2:2 (TxR:S)
Industry Standards	IEEE 802.3, IEEE 802.3u IEEE 802.11b/g/n IP67 certified
Chipset ID	Atheros - AR9341

Performance

Maximum Data Transfer Rate	300 Mbps
Max Distance	3.7 km (2.3 mi)
Bandwidth	20/40 MHz
Full Duplex Support	Yes
Frequency Range	2.4 ~ 2.4835 GHz



Modulation	OFDM, DSSS
Security Features	WEP Data Encryption TKIP/AES WPA and WPA2-PSK Data Encryption WPA and WPA2 Enterprise Data Encryption
Supported Protocols	CSMA/CA

Connector(s)

Connector Type(s)	Wireless N (IEEE 802.11n)
Internal Ports	RJ-45

Special Notes / Requirements

System and Cable Requirements	Available indoor AC electrical outlet Cat 5 (or better) network cabling from PoE Injector to Wireless AP and PoE Injector to LAN Switch/router (no more than 100m total)
-------------------------------	---

Indicators

LED Indicators	Wireless Signal Strength Power LAN Link / Activity
----------------	--

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	1 A
Output Voltage	48 DC
Output Current	0.5 A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In	13.5



Watts)

Environmental

Operating Temperature	-30C to 60C (-22F to 140F)
Storage Temperature	-30C to 85C (-22F to 185F)
Humidity	100% RH Non-Condensing

Physical Characteristics

Color	Gray
Material	Aluminum and Plastic
Product Length	6.3 in [16.1 cm]
Product Width	3.9 in [100.0 mm]
Product Height	2.3 in [58.0 mm]
Weight of Product	24.2 oz [686.0 g]

Packaging Information

Package Length	14.0 in [35.5 cm]
Package Width	8.3 in [21.2 cm]
Package Height	3.4 in [86.0 mm]
Shipping (Package) Weight	2.8 lb [1.2 kg]

What's in the Box

Included in Package	Outdoor Wireless Access Point
	PoE Injector
	Pole Mounting Kit
	Power Adapter
	Quick Start Guide

**Product appearance and specifications are subject to change without notice.*

