

14U Wall Mount Network Rack- 14" (35.5cm) Deep(Low Profile)- 19" Patch Panel Bracket for Shallow Server, ITEquipment, Network Switches- 77lbs/35kg WeightCap., Black

Product ID: RACK-14U-14-BRACKET



The 14U 14in (35.5cm) deep wall mounting bracket for patch panels delivers a sturdy and dependable equipment storage option, allowing you to wall mount data/IT equipment for a more efficient and accessible operating environment. It's the perfect solution for areas where space is at a premium like SoHo (small office, home office) environment, or space limited server room because it doesn't take any floor space.

The mounting bracket features an all-steel design and is suitable for mounting patch panels, or other slim 19in equipment to a wall, and to organize cabling or equipment in your network closet, wiring closet, back office, or IDF. The sturdy steel construction is especially helpful for durability and stability. Also, because The open frame wall rack's mounting holes are positioned 16in. apart, allowing you a simple and secure wall-stud anchoring to your existing construction framework.

M6 square cage nuts and M6 screws are included with the wall-mount bracket, additionally, M5x25 mounting screws are included to save you the hassle of sourcing separate mounting hardware.

Certifications, Reports and Compatibility

Applications

Features

- **14U WALL MOUNT RACK:** This 19-inch wide low profile wall mounted rack has a maximum mounting depth of 14in (35.5cm), recommended for networking equipment up to 12in (30cm) deep, leaving 2in (5.5cm) for cable routing; Maximum weight capacity of 77lbs (35kg)

- **EASY TO INSTALL:** 14U wall-mounting patch panel bracket ships fully assembled and comes with M6 screws and M6 square cage nuts for easier equipment installation; Includes wall mounting hardware; Predrilled wall mounting holes spaced 16" (40cm) apart
- **COLD-ROLLED STEEL CONSTRUCTION:** The wall mounting rack features a 1/16in (1.5mm) thick solid steel design for ultimate durability and to ensure a safe and sturdy mounting solution
- **EASY CABLE MANAGEMENT:** Built with efficiency in mind; Small wall mount patch panel bracket has rear cable opening slot for in-wall cable routing in your network closet, server room, wiring closet, classroom
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 14U wall mount rack is backed for life, including free 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
U Height	14U

Performance

Weight Capacity	77.2 lb [35 kg]
-----------------	-----------------

Physical Characteristics

Color	Black
Construction Material	Steel
Material	Steel
Product Length	19.7 in [50.0 cm]
Product Width	14.0 in [35.5 cm]
Product Height	24.6 in [62.5 cm]
Weight of Product	21.4 lb [9.7 kg]
Maximum Mounting Depth	11.8 in [30 cm]

Packaging Information

Package Quantity	1
Package Length	22.2 in [56.5 cm]

Package Width	16.5 in [42.0 cm]
Package Height	27.6 in [70.0 cm]
Shipping (Package) Weight	27.7 lb [12.6 kg]

What's in the Box

Included in Package	56 - M6 Cage Nuts
	56 - M6 Cage Screws
	56 - Plastic Washers
	4 - Plastic Wall Anchors
	4 - M5x25mm Mounting Screws
	1 - Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***