

2U Wall Mount Network Rack- 14In. Deep(Low Profile)- 19" Patch Panel Bracket for Shallow Server, ITEquipment, Network Switches- 77lbs/35kg WeightCapacity, Black

Product ID: RACK-2U-14-BRACKET



The 2U 14in deep wall mounting bracket for patch panels delivers a sturdy and dependable equipment storage option, allowing you to wall mount data/IT equipment for a more efficient and accessible operating environment. It's the perfect solution for areas where space is at a premium like SoHo (small office, home office) environment, or space limited server room because it doesn't take any floor space.

The mounting bracket features an all-steel design and is suitable for mounting patch panels, or other slim 19in equipment to a wall, and to organize cabling or equipment in your network closet, wiring closet, back office, or IDF. The sturdy steel construction is especially helpful for durability and stability. Also, because The open frame wall rack's mounting holes are positioned 16in. apart, allowing you a simple and secure wall-stud anchoring to your existing construction framework.

M6 square cage nuts and M6 screws are included with the wall-mount bracket, additionally, M5x25 mounting screws are included to save you the hassle of sourcing separate mounting hardware.

The RACK-2U-14-BRACKET is backed by a StarTech.com lifetime warranty and free lifetime technical support

Certifications, Reports and Compatibility

Applications

Features

- **2U WALL MOUNT RACK:** This 19-inch wide low profile wall mounted rack has a maximum mounting depth of 14 in (35 cm), recommended for networking equipment up to 12 in deep, leaving 2 in for cable routing; Maximum weight

capacity of 77 lbs (35 kg)

- **EASY TO INSTALL:** The 2U wall-mounting patch panel bracket ships fully assembled and comes complete with M6 screws and M6 square cage nuts for easier equipment installation & includes wall mounting hardware; Predrilled wall mounting holes spaced 16" apart
- **COLD-ROLLED STEEL CONSTRUCTION:** The wall mounting rack features a 1/16 in (1.5 mm) thick solid steel design for ultimate durability and to ensure a safe and sturdy mounting solution
- **EASY CABLE MANAGEMENT:** Built with efficiency in mind, the small wall mount patch panel bracket has rear cable opening slot for in-wall cable routing in your network closet, server room, wiring closet, classroom
- **STARTECH.COM ADVANTAGE:** IT professionals choice for over 30 years; This 2U wall mount rack backed for life by StarTech.com, including free 24/5 North America based multi-lingual tech support

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	2U
Mounting Rail Profile	G-Shape

Performance

Weight Capacity	77.2 lb [35 kg]
-----------------	-----------------

Physical Characteristics

Color	Black
Construction Material	Steel
Material	Steel
Product Length	19.7 in [50.0 cm]
Product Width	14.0 in [35.5 cm]
Product Height	3.7 in [9.3 cm]
Weight of Product	4.6 lb [2.1 kg]
Maximum Mounting Depth	11.8 in [30 cm]

Packaging Information

Package Quantity	1
Package Length	15.5 in [39.4 cm]
Package Width	20.9 in [53.2 cm]
Package Height	5.5 in [14.0 cm]
Shipping (Package) Weight	7.1 lb [3.2 kg]

What's in the Box

Included in Package	1 - Wall-mount rack
	8 - M6 Cage Nuts
	8 - M6 Cage Screws
	4 - M5x25mm Mounting Screws
	8 - Plastic Washers
	4 - Plastic Wall Anchors
	1 - Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***