

1U 15" Rackmount LCD Console - USB + PS/2

Product ID: RACKCONS1501



The RACKCONS1501 1U LCD Rack Console provides a complete keyboard, video and mouse control point, integrated neatly into only 1U of rack space, providing total KVM control right from your server rack.

The KVM rack console integrates a 15in TFT-LCD monitor, full 105-key keyboard and touchpad together into a durable rack-mountable console. When the console is not in use, it's as simple as folding the display down like a laptop computer and sliding it into your server rack or cabinet on sturdy mounting rails (included). To prevent unauthorized access to your connected systems, the console offers a key lock to secure the lid closed.

Offering consolidated control from a centralized location, the KVM console can be connected to virtually any multi-port KVM switch, for scalable connection to multiple servers/computers. Plus, the console supports connections to both PS/2 and USB controlled computers, accommodating both legacy and newer servers or KVM switches.

Backed by a Startech.com 2-year warranty, and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Centralized control of a single system, or dozens of PCs when connected to a KVM switch

- Improving the internal space-efficiency of existing cabinets
- Manage cabinet-mounted servers and KVM switches

Features

- Supports resolutions up to 1280x1024
- Key-lock to avoid unauthorized access
- Durable 1U rack-mountable design
- VGA video input support
- Compatible with USB or PS/2 PCs and KVMs
- 15" Active matrix TFT LCD display
- OSD (On Screen Display) controls for LCD display

Hardware

Warranty	2 Years
Front Door Key Lock	Yes
Audio	No
Display Size	15in
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	USB and PS/2
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	Yes
Daisy-Chain	Yes

Performance

On-Screen Display	Yes
IP Control	No

Maximum Analog Resolutions	1280x1024 @ 85Hz
Aspect Ratio	Standard (4:3)
Response Time	8ms
Contrast Ratio	400:1
Brightness	250 cd/m
Pixel Pitch Support	0.297 x 0.297 mm
Viewing Angle	160 (H), 130 (V)
Sync	45~80KHZ
Maximum Number of Users	1
Port Selection Support	Hotkeys and OSD (On Screen Display)
MTBF	60,000 Hours

Connector(s)

Console Interface(s)	2 - PS/2 (6 pin, Mini-DIN)
	1 - USB 2.0 Type-A (4 pin, 480Mbps)
	1 - VGA (15 pin, High Density D-Sub)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Power

Power Source	Standard 120V Power Cords
Input Voltage	110V-240V AC
Power Consumption (In Watts)	16

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)

Physical Characteristics

Color	Black
Material	Heavy Duty Steel
Product Length	20.9 in [53.0 cm]
Product Width	18.9 in [48.1 cm]
Product Height	1.8 in [4.5 cm]
Weight of Product	24.3 lb [11.0 kg]
Maximum Mounting Depth	31.5 in [80 cm]
Minimum Mounting Depth	21.7 in [55 cm]

Packaging Information

Package Quantity	1
Package Length	22.4 in [56.8 cm]
Package Width	26.2 in [66.5 cm]
Package Height	8.3 in [21.0 cm]
Shipping (Package) Weight	36.6 lb [16.6 kg]

What's in the Box

Included in Package	1 - 1U LCD Rack Console Drawer (1)
	1 - Mounting Rails - Set (1)
	1 - Console Cable Kit (1)
	1 - Power Adapter (1)

Warranty Information

Warranty	2 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***