

1U 17" Rackmount LCD Console - USB + PS/2

Product ID: RACKCONS1701



The RACKCONS1701 1U 17" Rack Mount LCD Console provides a complete keyboard, video and mouse control point, integrated neatly into only 1U of rack/cabinet space - providing complete KVM control right from a server rack.

Offering a durable, compactable 1U design, when the rack console is not in use it's as simple as folding the display like a laptop computer, and sliding it back into the server rack on the sturdy mounting rails (included). The included key lock provides an added security layer, helping to reduce unauthorized access to connected computers.

Offering consolidated control from a convenient location, the KVM rack console can be connected to virtually any multiport KVM switch, for control of multiple servers/computers, providing a scalable KVM control solution that lets you determine the type of KVM switch to use based on function and budget.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Centralized control of dozens of PCs and servers if used with optional KVM

- Managing cabinet mounted servers
- Improving the internal space efficiency of existing cabinets

Features

- Bright Active Matrix TFT Display
- Durable design
- Supports both USB and PS/2 connected servers or KVMs
- Security features, including port locking and auto scan
- OSD function (On Screen Display) for LCD display

Hardware

Warranty	2 Years
U Height	1U
Front Door Key Lock	Yes
Audio	No
Display Size	17in
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	USB and PS/2
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	Yes

Performance

On-Screen Display	Yes
IP Control	No
Maximum Analog Resolutions	1280x1024 @ 60Hz
Aspect Ratio	Standard (4:3)

Response Time	5ms
Contrast Ratio	1000:1
Brightness	250 cd/m
Color Depth	24-bit, 16.7M colors (Truecolor)
Pixel Pitch Support	0.264 x 0.264 mm
Viewing Angle	170 (H), 160 (V)
Port Selection Support	Hotkeys and OSD (On Screen Display)
MTBF	60,000 Hours

Connector(s)

Host Connectors	2 - PS/2 (6 pin, Mini-DIN)
	1 - USB 2.0 Type-A (4 pin, 480Mbps)
	1 - VGA (15 pin, High Density D-Sub)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Power

Power Source	AC Adapter Included
Input Voltage	115V-230V AC
Center Tip Polarity	Positive

Environmental

Operating Temperature	0 ~ 50 C / 32 ~ 122 F
Storage Temperature	20 ~ 60 C / -4 ~ 140 F

Physical Characteristics

Color	Black
Material	Heavy Duty Steel
Cable Length	6ft (1.83m) Console Cable Kit
Product Length	20.9 in [53.0 cm]

Product Width	18.9 in [48.1 cm]
Product Height	1.8 in [4.5 cm]
Weight of Product	26.5 lb [12.0 kg]
Maximum Mounting Depth	31.5 in [80 cm]
Minimum Mounting Depth	21.7 in [55 cm]

Packaging Information

Package Quantity	1
Package Length	22.4 in [56.8 cm]
Package Width	26.2 in [66.5 cm]
Package Height	8.3 in [21.0 cm]
Shipping (Package) Weight	38.0 lb [17.2 kg]

What's in the Box

Included in Package	1 - 1U LCD Rack Console Drawer
	1 - Mounting Rails - Set
	1 - Console Cable Kit
	1 - Power Cord

****Product appearance and specifications are subject to change without notice.***