

6ft (2m) Power Extension Cord, Right Angle NEMA 5-15P to NEMA 5-15R, 13A 125V, 16AWG, Computer Power Extension Cord, Flat Extension Cord, AC Outlet Extension Cable

Product ID: RFX-6F-POWER-CORD



Configure the NEMA 5-15 power connections in a server room, reduce cable strain for safe and efficient power connections behind office furniture, and extend the length of bulky power cords.

The extension cord features a low-profile right-angled NEMA 5-15 plug. This reduces cable strain and increases the amount of airflow when connecting to a NEMA 5-15 receptacle that is situated behind a cabinet or a desk within a high-density server rack in a data center. Extend any NEMA 5-15 power cord (e.g., for a computer, display, server PDU/UPS, etc.).

The right-angle power cord enables access to previously blocked receptacles, located on power strips, surge protectors, or wall outlets. Since the cable is situated to the side of the outlet, bulky plugs will no longer impede access to nearby receptacles.

This product is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

Features

• AC POWER EXTENSION CORD: This 6ft (1.8m) 16AWG AC power extension cord with Right-Angle NEMA 5-15P



and NEMA 5-15R connectors is suitable for workstations/home offices. Indoor use only. Rated to carry 125V at 13A

- PERFORMANCE AND SAFETY: UL listed components Fully molded strain relief connectors for durability Fire Rating: VW-1 3 Conductor extension cord made with 100% copper wire This power extension cord is available in 1ft and 3ft
- SPECS: 6ft (1.8m) AC Power Cord Right-Angle NEMA 5-15P to NEMA 5-15R 16AWG 125V 13A (Max) Jacket Type: SJT Jacket Material: PVC Black Temperature Range: 14F to 95F (-10C to 35C) Cable Outer Diameter: 0.33in (8.4mm)
- COMPATIBILITY: PC Power Extension Cord NEMA 5-15P works with North American outlets Extend a 3-prong power connection from your desktop computer, server, or printer Replacement power supply cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

| Hardware | | |
|---------------|-----------------------|-------------------------------------|
| | Warranty | Lifetime |
| | Number of Conductors | 3 |
| | Connector Plating | Nickel |
| | Cable Jacket Material | PVC - Polyvinyl Chloride |
| | Fire Rating | VW-1 Rated |
| | Cable Type | SJT |
| Connector(s) | | |
| | Connector A | 1 - NEMA 5-15 Power (North America) |
| | Connector B | 1 - NEMA 5-15 Power (North America) |
| Power | | |
| | Input Voltage | 125 AC |
| | Input Current | 13 A |
| Environmental | | |
| | Operating Temperature | -10 to 35C (14 to 95F) |
| | Storage Temperature | -20 to 60C (-4 to 140F) |
| | Humidity | 5~95% |
| | | |

Physical Characteristics



Color Black

Connector Style Right Angle to Straight

Wire Gauge 16 AWG

Cable OD 0.3 in [8.5 mm]

Product Length 6.0 ft [1.8 m]

Product Width 1.0 in [2.6 cm]

Product Height 1.4 in [3.5 cm]

Weight of Product 9.2 oz [262.0 g]

Packaging Information

Package Quantity 1

Package Length 5.5 in [14.0 cm]

Package Width 12.2 in [31.0 cm]

Package Height 2.0 in [5.0 cm]

Shipping (Package)

Weight

9.5 oz [270.0 g]

What's in the Box

Included in Package 1 - Power Extension Cable

^{*}Product appearance and specifications are subject to change without notice.