

1m Premium Certified HDMI 2.0 Cable with Ethernet - Durable High Speed UHD 4K 60Hz HDR - 3ft Rugged M/M HDMI Cord with Aramid Fiber - TPE - Ultra HD Monitors, TVs & Displays

Product ID: RHDMM1MP



This 3 ft. (1 m) High Speed HDMI Cable with Ethernet withstands the daily demands of connecting your HDMI devices. Tested to endure strenuous wear and tear, the rugged cable is a must-have for both business and consumer applications.

The HDMI Premium Certified cable has aramid fiber reinforcement that braces it from the stress of frequent bends from hooking up your TV or monitor. This also lets the cord flex without over-stretching or damaging the core of the cable.

- Aramid fiber adds strength and durability to the cable
- Insulated conductors reduce friction, provide more flexibility
- EMI protection with aluminum-mylar foil with braided shielding
- TPE cable jacket is more flexible than a standard PVC cable

The high quality cable is constructed to prevent the connector from separating from the jacket. The extra-long strain relief molding is tested to withstand over 10,000+ bend cycles at a 180 angle.

- HDMI gold plated connector with metal shield protects the circuit board from EMI and reinforces the connection point
- Strain relief tested to tolerate over 10,000+ bend cycles at a 180 angle

Supporting all HDMI 2.0 specifications, this HDMI Premium Certified adapter cable supports resolutions up to 4K 60Hz with a bandwidth of up to 18Gbps. The HDMI cable also supports HDR for higher contrast ratio and vivid colors

providing an enriched and enjoyable viewing experience.

RHDMM1MP is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Note: DuPont and Kevlar are trademarks or registered trademarks of E.I. du Pont de Nemours and Company.

Certifications, Reports and Compatibility

Applications

- Connect 4K/Ultra HD displays and devices

Features

- **PREMIUM HDMI 2.0 CABLE:** Certified HDMI 2.0 with Ethernet w/18Gbps bandwidth; 4K 60Hz (3840x2160), HDR for high contrast ratio, 21:9 cinema aspect ratio, 3D, 32 Ch. multi-stream audio w/1536Hz sampling
- **DURABLE:** Ultra HD high speed HDMI cable w/Kevlar aramid fiber for high tensile (pull) strength for reliability & durability; Tested to withstand 10000+ bend cycles at 180 angle & 5000+ insertions
- **FLEXIBLE CABLE:** TPE jacket absorbs stress of frequent bends protecting the core of the rugged UHD HDMI cord. TPE is non-toxic, halogen free & RoHS certified for environmental sustainability
- **APPLICATIONS:** Ideal for home/office & travel, works w/your laptop for presentations via monitors, projector or large display w/ CEC functions; Compatible w/ HDMI 1.4 1080p HD & previous HDMI versions
- **SPECS:** 1 m (3.3 ft) Black HDMI 2.0 HDMI Male to Male 30 AWG Reinforcement: Aramid Fiber Jacket: TPE EMI Shielding Audio Return Channel (ARC) BT.200 colorimetry Lifetime Warranty

Prominence

Warranty	Lifetime
Description CDW 75 - 1st Line	StarTech.com 3ft Certified Premium High Speed HDMI 2.0 Cable 4K HDR Durable

Hardware

Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Audio Specifications	Up to 32 audio channels with 1536Hz sampling rate
----------------------	---

Connector(s)

Connector A	HDMI (19 pin)
	HDMI (19 pin)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	30 AWG
Cable Length	39.4 in [100 cm]
Product Length	39.4 in [100.0 cm]
Product Width	0.7 in [17 mm]
Product Height	0.2 in [5 mm]
Weight of Product	1.2 oz [33 g]

Packaging Information

Package Length	5.9 in [15 cm]
Package Width	0.8 in [20 mm]
Package Height	8.1 in [20.5 cm]
Shipping (Package) Weight	2.9 oz [82 g]

What's in the Box

Included in Package	HDMI Cable
---------------------	------------

**Product appearance and specifications are subject to change without notice.*

