


## Cat5e Patch Cable with Snagless RJ45 Connectors - 20 ft, Blue

ID prodotto: RJ45PATCH20



This 20-foot Cat5e cable meets or exceeds all Category 5e cable specifications to ensure reliable Ethernet network connections. Plus, the cable features a durable blue PVC jacket that enables you to color code your network cable runs as needed.

For easier cable runs, the snagless connectors protect the cable's RJ45 clips during installation, making them less likely to snag or break. This ensures a sturdy connection by preventing the cable from becoming loose from the port.

The cable features moulded boots that offer connector strain relief, by stopping the RJ45 connector termination points from bending at sharp angles, and reducing the risk of damage to the cable, which could decrease network performance.

Get the highest value for your cable investment with our Cat 5e cables, each one manufactured using high-quality copper conductors.

Ensure high-performance capability for your demanding Ethernet applications, such as Power-over-Ethernet, using cables that include 24 AWG copper.

Rely on our RJ45 connectors to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

The RJ45PATCH20 is backed by StarTech.com's lifetime warranty for guaranteed reliability.

## Certificazioni, report e compatibilità



## Applicazioni

- Designed for use with Fast Ethernet networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet
- Extend the reach of your Ethernet network devices by 20 ft

## Caratteristiche

- RJ45 connector clip protectors
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Colored hoods for departmental color coding
- Molded strain relief prevents the cable from being bent at sharp angles at the RJ45 connector, to minimize the stress at the plug termination point
- Constructed with top quality components
- High quality 24 AWG copper wire

### Hardware

Norme di garanzia	Lifetime
Numero di conduttori	4 Pair UTP
Tipo guaina cavo	PVC - Polyvinyl Chloride
Classe di resistenza al fuoco	Classe CM
Tipo cavo	Antigroviglio

### Connettore/i

Connettore A	1 - RJ-45
Connettore B	1 - RJ-45

---

Caratteristiche fisiche

Colore	Blu
Diametro filo	24 AWG
Lunghezza del cavo	20.0 ft [6.1 m]
Lunghezza prodotto	20.0 ft [6.1 m]
Larghezza prodotto	0.5 in [1.2 cm]
Altezza prodotto	0.5 in [1.4 cm]
Peso prodotto	7.4 oz [210.0 g]

---

Informazioni confezione

Quantità confezione	1
Lunghezza Confezione	7.6 in [19.2 cm]
Larghezza del Pacco	7.9 in [20.0 cm]
Altezza del Pacco	1.2 in [3.1 cm]
Peso spedizione (confezione)	6.9 oz [196.0 g]

---

Contenuto della confezione

Incluso nella confezione	1 - 20 ft. Cat5e Patch Cable - Blue
--------------------------	-------------------------------------

---

Informazioni sulla garanzia

Warranty	A vita
----------	--------

---

\* L'aspetto e le specifiche dell'articolo sono soggetti a modifiche senza preavviso.