

## Cat5e Patch Cable with Snagless RJ45 Connectors - 6 ft, Blue

Produkt ID: RJ45PATCH6



The 45PATCH6BL Cat5e Patch Cable (6 ft) meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable blue PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features a snagless design that protects the RJ45 connector clips from damage and makes the cable less prone to snagging during installation. The cable also features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat5e Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This RJ45 patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

### Certifikat, rapporter och kompatibilitet



## Användning

- Framtagen för att användas med snabba Ethernet-nätverk
- Kopplar från hubb till distributionspanel
- Anslut en arbetsstation till ett vägguttag

## Funktioner

- Skydd till RJ45-kontakter
- Tillverkad och testad med omsorg för att bakåtöverhörning (NEXT) ska ligga väl inom godkända gränser
- Färgade huvor så att man kan färgkoda olika avdelningar
- Gjuten dragavlastning hindrar att kabeln böjs i skarpa vinklar vid RJ45-kontakten, vilket i sin tur minskar påfrestningarna på kontaktens spets
- Tillverkad av komponenter med toppkvalitet
- Högkvalitativ 0,25 mm<sup>2</sup> koppartråd

---

### Hårdvara

|                    |                          |
|--------------------|--------------------------|
| Garantipolicy      | Lifetime                 |
| Antal ledare       | 4 Pair UTP               |
| Kabelmanteltyp     | PVC - Polyvinyl Chloride |
| Brandteknisk klass | CM-klass                 |
| Kabeltyp           | Hakfri                   |

---

### Prestanda

|                     |                 |
|---------------------|-----------------|
| Kabelklassificering | CAT5e - 350 MHz |
|---------------------|-----------------|

---

### Kontakt(er)

|             |           |
|-------------|-----------|
| Connector A | 1 - RJ-45 |
| Connector B | 1 - RJ-45 |

#### Utseende

|               |                 |
|---------------|-----------------|
| Färg          | Blå             |
| Tråddimension | 24 AWG          |
| Kabellängd    | 6.0 ft [1.8 m]  |
| Produktlängd  | 6.0 ft [1.8 m]  |
| Produktbredd  | 0.5 in [1.2 cm] |
| Produkthöjd   | 0.5 in [1.4 cm] |
| Produktvikt   | 2.4 oz [68.0 g] |

#### Förpackning

|                         |                  |
|-------------------------|------------------|
| Förpackningsantal       | 1                |
| Paketets längd          | 6.3 in [16.0 cm] |
| Paketets bredd          | 7.8 in [19.8 cm] |
| Paketets höjd           | 0.9 in [2.2 cm]  |
| Fraktvikt (förpackning) | 2.5 oz [72.0 g]  |

#### Vad det är i lådan

|                 |                                        |
|-----------------|----------------------------------------|
| Ingår i paketet | 1 - 6 Ft Blue RJ45 Cat. 5E Patch cable |
|-----------------|----------------------------------------|

#### Warranty Information

|          |           |
|----------|-----------|
| Warranty | Livslängd |
|----------|-----------|

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.