

## 1U 19in Steel Vertical Wall Mount Equipment Rack Bracket

Product ID: RK119WALLV



The RK119WALLV 1U 19in Steel Vertical Wall Mount Equipment Rack Bracket offers a versatile storage solution allowing rackmount equipment (Network devices, power strips, patch panels) to be mounted vertically (flush with wall) to save space. Alternatively, the 1U bracket can be installed horizontally under a desk, making it easy to access installed equipment directly from your workspace. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Perfect for SoHo (small office, home office) environments, the wallmount bracket features a sturdy steel design constructed to EIA-310 19in rack standards, and offers space-savings for environments lacking the footprint space for a full size server equipment rack. Suitable for mounting on virtually any wall/ceiling surface (e.g. drywall), the bracket mounting holes are positioned at exactly 16in apart, matching standard construction framework.

Backed by a StarTech.com Lifetime Warranty.

Need more storage space? StarTech.com also offers a [%product id="RK219WALLV" text="2U 19in Wallmount Bracket"%], a [%product id="RK319WALLV" text="3U 19in Wallmount Bracket"%] and a [%product id="RK419WALLV" text="4U 19in Wallmount Bracket"%].

### Certifications, Reports and Compatibility



### Applications

- Mount networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Ideal for small and medium businesses needing rack solutions

## Features

- Constructed to meet EIA-310 19" rack standards
- Made from solid steel for durability
- Compatible with most 19" rack mountable equipment
- Arrives fully assembled with cage screws and nuts for mounting equipment
- Wall mounting holes are 16" center to center for greater stability, and mounting into standard wall studs
- Equipment can be vertically wall mounted, or horizontally under a desk
- TAA compliant for GSA Schedule purchases

<b>Hardware</b>	Warranty	Lifetime
	Wallmountable	Yes
	Rack Type	2-Post
	Frame Type	Open Frame
	U Height	1U
	Mounting Rail Profile	L-Shape
	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
<b>Performance</b>	Weight Capacity	125.3 lb [56.7 kg]
	<b>Special Notes / Requirements</b>	Note Package includes 1 " screws for mounting to wood surfaces, additional hardware will be required for other materials
<b>Physical Characteristics</b>	Color	Black
	Construction Material	Steel
<b>Product Measurements</b>	Product Length	5.9 in [1.5 cm]
	Product Width	19.8 in [5.0 cm]
	Product Height	2.3 in [59 mm]
	Weight of Product	23.8 oz [675.171 g]
<b>Packaging Information</b>	Flat Pack (Assembly Required)	No
	Package Length	20.4 in [5.2 cm]
	Package Width	6.6 in [1.7 cm]
	Package Height	2.8 in [71 mm]
	Shipping (Package) Weight	34.4 oz [973.862 g]

---

<b>What's in the Box</b>	Included in Package	Vertical Wall Mount Bracket
	Included in Package	Wood Screws
	Included in Package	M5 Screws
	Included in Package	M5 Cage Nuts
	Included in Package	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

