

12U 19in Hinged Wall Mount Server Rack Cabinet w/ Vented Glass Door

Produkt ID: RK1219WALH



This 12U Rack offers a durable solution for mounting valuable server equipment, routers, switches and other networking equipment while saving space and hassle. The sturdy 12U rack features a high quality steel design and a vented, tempered glass door to help keep your rack mount equipment safe and cool.

A suitable addition to any server room, wiring closet, manufacturing area, warehouse or locale where networking equipment requires an added level of protection, the 12U rack accommodates 19" wall mount devices (19" depth) and features a rear-hinged design that makes it easier to access cabling and device ports.

Certifikat, rapporter och kompatibilitet

Användning

- Mounting standard 19 in. networking equipment in exposed or insecure locations

Funktioner

- Unique hinged design swings open for easy access to a your equipment
- Cable pass-through at rear of cabinet
- Fan mounts for optional additional cooling
- Sturdy steel design

- Tempered, vented, lockable glass front door
- Removable side panels with lock.

Hårdvara

Garantipolicy	Lifetime
Väggmonterbar	Ja
Hylltyp	4 stag
Ramtyp	Inneslutet skåp
U-höjd	12U
Specialfunktioner	Justerbara monteringsrännor Ships Fully Assembled Kan monteras på väggen
Profil monteringskenor	L-Shape
Kylningsalternativ	Två tillvalsfläktar: 120 mm
Mounting Hole Types	Kvadrat (för burmutter)
Industristandarder	EIA/ECA-310-E

Prestanda

Weight Capacity	132.6 lb [60 kg]
-----------------	------------------

Utseende

Färg	Grå
Främre dörr	Stål med glasfönster
Främre dörrfunktioner	Säkert nyckellås med vändbar och avtagbar främre dörr
Sidopaneler	Stål
Sidopanelfunktioner	Säkert nyckellås med avtagbara sidopaneler
Bakre dörr	Stål

Bakre dörrfunktioner Säkert nyckellås

Product
Measurements

Inre bredd	23.4 in [59.5 cm]
Inre djup	21.2 in [53.8 cm]
Produktlängd	22.2 in [56.4 cm]
Produktbredd	22.0 in [55.9 cm]
Produkt höjd	25.0 in [63.6 cm]
Produktvikt	58.1 lb [26.3 kg]
Maximalt monteringsdjup	15.5 in [39.3 cm]
Minsta monteringsdjup	0.5 in [12 mm]

Förpackning

Platt paket (montering krävs)	Nej
Package Length	26.9 in [68.2 cm]
Package Width	26.3 in [66.7 cm]
Package Height	27.0 in [68.6 cm]
Fraktvikt (förpackning)	64.2 lb [29.0 kg]

Vad det är i lådan

Ingår i paketet	12U Server Cabinet
	Sets of Keys
	M6 skruvar
	M6 korgmuttrar
	Torxverktyg
	insexnyckel



* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

