

## 12U 19in Hinged Wall Mount Server Rack Cabinet w/ Vented Glass Door

**Product ID:** RK1219WALH



This 12U Rack offers a durable solution for mounting valuable server equipment, routers, switches and other networking equipment while saving space and hassle. The sturdy 12U rack features a high quality steel design and a vented, tempered glass door to help keep your rack mount equipment safe and cool.

A suitable addition to any server room, wiring closet, manufacturing area, warehouse or locale where networking equipment requires an added level of protection, the 12U rack accommodates 19" wall mount devices (19" depth) and features a rear-hinged design that makes it easier to access cabling and device ports.

### **Certifications, Reports and Compatibility**

### **Applications**

- Mounting standard 19 in. networking equipment in exposed or insecure locations

### **Features**

- Cable pass-through at rear of cabinet
- Fan mounts for optional additional cooling
- Sturdy steel design
- Tempered, vented, lockable glass front door
- Unique hinged design swings open for easy access to a your equipment
- Removable side panels with lock.

---

**Hardware**

Warranty	Lifetime
Wallmountable	Yes
Rack Type	4-Post
Frame Type	Aluminum
U Height	12U
Special Features	Adjustable Mounting Rails
	Wall-Mountable
	Ships Fully Assembled
Mounting Rail Profile	L-Shape
Fan Options	Two Optional Fans: 120 mm
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

**Performance**

Weight Capacity	132.6 lb [60 kg]
-----------------	------------------

---

**Physical Characteristics**

Color	Gray
Front Door Construction	Steel with Glass/Acrylic Window
Front Door Features	Secure Key Lock with Reversible and Removable Front Door
Side Panel Construction	Steel
Side Panel Features	Secure Key Lock with Removable Side Panels
Rear Door Construction	Steel
Rear Door Features	Secure Key Lock

---

**Product Measurements**

Internal Width	23.4 in [59.5 cm]
----------------	-------------------



Internal Depth	21.2 in [53.8 cm]
Product Length	22.2 in [56.4 cm]
Product Width	22.0 in [55.9 cm]
Product Height	25.0 in [63.6 cm]
Weight of Product	58.1 lb [26.3 kg]
Maximum Mounting Depth	15.5 in [39.3 cm]
Minimum Mounting Depth	0.5 in [12 mm]

---

**Packaging Information**

Flat Pack (Assembly Required)	No
Package Length	26.9 in [68.2 cm]
Package Width	26.3 in [66.7 cm]
Package Height	27.0 in [68.6 cm]
Shipping (Package) Weight	64.2 lb [29.0 kg]

---

**What's in the Box**

Included in Package	12U Server Cabinet
	Sets of Keys
	M6 Screws
	M6 Cage Nuts
	Torx Tool
	Hex Key

---

***\*Product appearance and specifications are subject to change without notice.***

