

Refurbished 12U 19in Hinged Wall Mount Server Rack Cabinet w/ Vented Glass Door

Product ID: RK1219WALHR



Refurbished cabinets may have minor scratches and dents similar to photos.

This refurbished 12U Rack offers a durable solution for mounting valuable server equipment, routers, switches and other networking equipment while saving space and hassle. The sturdy 12U rack features a high quality steel design and a vented, tempered glass door to help keep your rack mount equipment safe and cool.

A suitable addition to any server room, wiring closet, manufacturing area, warehouse or locale where networking equipment requires an added level of protection, the 12U rack accommodates 19" wall mount devices (19" depth) and features a rear-hinged design that makes it easier to access cabling and device ports.

Every refurbished server rack includes complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the paint on the metal casing, but all other components are as new. Backed by a 90-day replacement warranty,.

Certifications, Reports and Compatibility



Applications

- Mounting standard 19 in. networking equipment in exposed or insecure locations
- Data centers
- Industrial control centers
- Telecommunication closets

- Audio/Visual control centers

Features

- Unique hinged design swings open for easy access to a your equipment
- Cable pass-through at rear of cabinet
- Fan mounts for optional additional cooling
- Removable side panels with lock.
- Sturdy steel design
- Tempered, vented, lockable glass front door

Hardware

Warranty	None
Wallmountable	Yes
Rack Type	4-Post
Frame Type	Steel
U Height	12U
Front Door Construction	Steel with Glass/Acrylic Window
Front Door Features	Secure Key Lock
Side Panel Construction	Steel
Fan(s)	Optional
Industry Standards	EIA RS310-C

Performance

Weight Capacity (Stationary)	132.3 lb [60 kg]
---------------------------------	------------------

Physical Characteristics

Color	Beige
Internal Width	18.3 in [46.5 cm]
Weight of Product	65.0 lb [29.5 kg]

Maximum Mounting Depth 16.2 in [41.3 cm]

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	22.8 in [58 cm]
Package Width	24.6 in [62.5 cm]
Package Height	26.0 in [66 cm]
Shipping (Package) Weight	68.1 lb [30.9 kg]

What's in the Box

Included in Package	1 - 19in Cabinet
	1 - Package of Cab screws and Cage Nuts
	1 - Keys

****Product appearance and specifications are subject to change without notice.***