

Refurbished 12U 36in Knock-Down Server Rack Cabinet with Casters

Product ID: RK1236BKFR



Refurbished cabinets may have minor scratches and dents.

The RK1236BKFR Refurbished 12U 36in Knock-Down Server Rack Cabinet with Casters features a vented acrylic front door and mesh rear door, to provide devices stored in the cabinet with cost-effective passive cooling as well as offer security for your valuable equipment.

Supporting a total load capacity of 800 kg (1760 lbs), the server rack is constructed of steel and aluminum to ensure a sturdy platform for valuable server/networking equipment. The included casters make this product a flexible rack solution for any IT environment or server closet.

The rack is easy to assemble at the point of installation for rapid deployment and features a flat-packed design that helps to minimize shipping costs.

Every refurbished server rack includes complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the paint on the metal casing, but all other components are as new. Backed by a 90-day replacement warranty.

Certifications, Reports and Compatibility



Applications

- Perfect solution for Technology shops and repair centers with limited space and mountable equipment where security is required
- Ideal for rack mount servers, KVM switches, networking equipment and cabinet consoles

- Audio/Video editing room, radio or television studio broadcast rackmount equipment
- A great solution for the college/university classroom, where only limited rackmount equipment is needed, but security is still important

Features

- Includes casters and stabilizer feet
- Flat packed into a single carton for easy shipping
- Vented doors and side panels
- Adjustable mounting rails
- Quick and easy to assemble

Hardware

Warranty	None
Wallmountable	No
Rack Type	4-Post
Frame Type	Enclosed Cabinet
U Height	12U
Special Features	Casters (Included)
	Easy Assembly
	Grounding Lug(s)
	Leveling Feet
Mounting Rail Profile	U-Markings
	G-Shape
	Square (For Cage Nut)
Mounting Hole Types	
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity (Stationary)	1764.0 lb [800 kg]
------------------------------	--------------------

Physical Characteristics

Color	Black
Front Door Construction	Steel with Glass Window
Front Door Features	Secure Key Lock with Removable Front Door
Side Panel Construction	Aluminum
Side Panel Features	Secure Key Lock with Removable Side Panels
Rear Door Construction	Steel Mesh
Rear Door Features	Secure Key Lock with Removable Back Door

Product Measurements

Internal Width	23.6 in [60 cm]
Internal Depth	29.1 in [74 cm]
Product Length	35.4 in [90.0 cm]
Product Width	23.7 in [60.3 cm]
Product Height	26.1 in [66.3 cm]
Weight of Product	96.0 lb [43.5 kg]
Maximum Mounting Depth	29.1 in [74 cm]
Minimum Mounting Depth	5.5 in [14 cm]
Product Height with Casters	28.9 in [73.4 cm]

Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	38.3 in [97.4 cm]
Package Width	28.9 in [73.4 cm]
Package Height	12.7 in [32.2 cm]
Shipping (Package) Weight	116.0 lb [52.6 kg]

What's in the Box

Included in Package	3 - Bottom Panel
	2 - Side Panel and Frame
	1 - Top Panel
	4 - Cross Brace
	8 - Plastic Corner Caps
	4 - Casters
	2 - Sets of Keys
	4 - Adjustable Feet
	1 - Bag M6 Cab Screws and Nuts
	2 - Allen Wrench
	1 - Assembly Screw Kit

Warranty Information

Warranty	Refurbished 90 Days
----------	---------------------

****Product appearance and specifications are subject to change without notice.***