

15U 19" Wall Mount Network Cabinet - 16" Deep Hinged Locking IT Network Switch Depth Enclosure - Assembled Vented Computer Equipment Data Rack w/Shelf & Flexible Side Panels

Product ID: RK1520WALHM



This 15U server or network rack cabinet lets you mount your EIA-310 compliant equipment to the wall, in a secure enclosure that has a hinged rear door for easy access to your equipment. The enclosure features adjustable mounting depth from 2 to 16 in. to provide a robust storage solution for your rack-mount equipment.

To provide secure stability for your heaviest equipment, this rack offers 4-post mounting, supporting a higher weight capacity per U than 2-post racks and supporting a total load capacity of up to 200 lbs. (90 kg).

Save valuable floor space by wall-mounting the enclosure. The wall-mounted design makes this enclosure the ideal solution for optimizing equipment storage in your classroom, retail store, server room or office. This rack also includes a 1U shelf that gives you a stable surface for placing equipment that's not rack-mountable or storing your tools.

The wall-mount network rack makes it easy to access your equipment and cabling, with a rear hinge that swings the enclosure away from the wall. By flipping the enclosure 180 degrees upon installation, you can reverse the direction of the hinge so that the enclosure can swing open from left or the right, depending upon your preference.

The 15U network cabinet features a removable and reversible front door and removable side panels, each with quick-release mechanisms, so you can easily access your equipment. Plus, each door and panel on this rack features an independent lock, ensuring your equipment is secure.

For hassle-free cable management, the rack includes a 3-meter roll of hook-and-loop cable tie that makes it easy to keep your cables neat and tidy by binding them together or binding them to the rack. The self-gripping fabric can be cut to any size, enabling a wrap-around solution for the cables of any rack-mount equipment.

This server rack enclosure features heavy-duty steel construction, with lockable doors at all entrances. For hassle-free equipment installation, the mounting rails on the rack can be switched for use with square holes and cage nuts, or tapped rails.

To ensure your equipment is running at an optimal temperature, the server rack/cabinet promotes passive cooling. It features mesh doors and vented top and bottom panels for maximum airflow.

For simple and sturdy mounting, the rack's mounting holes are positioned 16 in. apart, so you can securely attach it to a wall using wall studs.

The RK1520WALHM is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Wall-mount your server and networking equipment flush against the wall, in areas with limited space such as technology store fronts or repair centers
- Install the rack in your small office environment, where you can't fit a full-sized rack
- Organize cabling or equipment in your network closet, wiring closet, back office or IDF

Features

- **CONVENIENT & SECURE ACCESS:** Wall mount network cabinet w/ 180 hinged design provides easy lockable access to rear of mounted devices. Flexible enclosure also features removable doors & side panels.
- **ACCESSORIES INCLUDED:** IT Data Rack includes complete set of accessories: a shelf (CABSHELFV1U), roll of hook-and-loop fastener, 50 cage nuts and screws, & 2 pairs of keys for the front and side panels
- **STURDY CONSTRUCTION:** 15U 19" EIA/ECA-310-E enclosed design, 200lb weight capacity, 21" deep with a max. 16" mounting depth, removable sides, locking reversible door, dual top cable hole, optional fans
- **DESIGNED FOR COOLING:** The switch depth vented rack has mesh front doors and side panels to provide fresh airflow and supports active cooling with up to four optional 120mm fans (ACFANKIT12)
- **PRE-ASSEMBLED:** This IT cabinet comes fully assembled out of the box and the included hardware allows for quick installation of server room rackmount or computer equipment without additional purchases

Hardware

| | |
|------------------|--|
| Warranty | 5 Years |
| Wallmountable | Yes |
| Rack Type | 4-Post |
| Frame Type | Enclosed Cabinet |
| U Height | 15U |
| Special Features | Adjustable Mounting Rails Built-in Cable Management |

| | |
|-----------------------|----------------------------|
| | Grounding Lug(s) |
| | U-Markings |
| | Wall-Mountable |
| | Ships Fully Assembled |
| Mounting Rail Profile | L-Shape |
| Fan Options | Four Optional Fans: 120 mm |
| Mounting Hole Types | Square (For Cage Nut) |
| | Threaded Hole |
| Industry Standards | EIA/ECA-310-E |

Performance

| | |
|-----------------|------------------|
| Weight Capacity | 198.9 lb [90 kg] |
|-----------------|------------------|

Special Notes / Requirements

| | |
|------|--|
| Note | Includes CABSHELFV1U and 2 pairs of keys |
|------|--|

Physical Characteristics

| | |
|-------------------------|--|
| Color | Black |
| Front Door Construction | Steel Mesh |
| Front Door Features | Secure Key Lock with Reversible and Removable Front Door |
| Side Panel Construction | Steel Mesh |
| Side Panel Features | Secure Key Lock with Removable Side Panels |
| Rear Door Construction | Steel |
| Rear Door Features | Secure Key Lock |

Product Measurements

| | |
|----------------|-------------------|
| Internal Width | 23.5 in [59.6 cm] |
| Internal Depth | 21.5 in [54.7 cm] |
| Product Length | 21.8 in [55.3 cm] |



| | |
|------------------------|-------------------|
| Product Width | 24.0 in [61.0 cm] |
| Product Height | 30.4 in [77.2 cm] |
| Weight of Product | 87.5 lb [39.6 kg] |
| Maximum Mounting Depth | 16.1 in [41 cm] |
| Minimum Mounting Depth | 2.4 in [60 mm] |

Packaging Information

| | |
|-------------------------------|--------------------|
| Flat Pack (Assembly Required) | No |
| Package Length | 26.6 in [67.5 cm] |
| Package Width | 25.0 in [63.5 cm] |
| Package Height | 33.7 in [85.5 cm] |
| Shipping (Package) Weight | 185.6 lb [84.0 kg] |

What's in the Box

| | |
|---------------------|----------------------|
| Included in Package | wall-mount enclosure |
| | 1U shelf |
| | 10 ft hook and loop |
| | 12-24 cage nuts |
| | 12-24 screws |
| | door keys |
| | side panel keys |
| | instruction manual |

****Product appearance and specifications are subject to change without notice.***

