

2-Post 15U Heavy-Duty Wall Mount Network Rack, 19" Open Frame Server Rack with Adjustable Depth, Wall Mount Data Rack for IT / AV / Patch Panel / Computer Equipment - Cage Nuts and Screws Included

Product ID: RK15WALLOA



This open frame wallmount server rack provides 15U of storage, helping you to save space and stay organized. The equipment rack features an adjustable depth and can hold a total of up to 198 lb (90 kg).

The open frame rack adjusts from 12 to 20 inches (30.4 to 50.8 cm) to accommodate larger data, network, and telecommunication devices. The above-average depth also gives you the option to mount shelves and other accessories.

When space is limited you can wall-mount the open-frame rack in a server room, office, or above a doorway, to expand your workspace and ensure your equipment is easy to access.

The rack's open frame design promotes passive cooling; ensures easy access to your rack-mounted equipment and makes it simple to configure mounted devices, which saves you time.

With an adjustable depth as low as 12 inches (30.4 cm), this network rack is perfect for smaller spaces. It's easy to assemble and features wall-mounting holes that are spaced 12 and 16 in. apart, making it suitable for mounting on almost any wall, based on North American wall-frame stud-spacing standards.

Certifications, Reports and Compatibility



Applications

- Small office spaces

- When floor space is limited

Features

- **ADJUSTABLE DEPTH:** This 2-post 15U 19 inch open frame network rack is EIA/ECA-310 compliant and has an adjustable depth (12-20in / 30.5-50.8cm); Data rack is ideal for AV / Audio / IT / computer equipment, servers, switches, patch panels, and PDUs
- **HEAVY DUTY:** Durable rack features a vertical rail made of SPCC cold-rolled steel and a weight capacity of up to 200lbs/90kg; Its design supports unobstructed airflow to help keep your equipment cool and easy to install with access to all sides
- **EFFICIENT FLAT PACK SHIPPING:** The IT rack ships flat packed with ISTA-6 certified packaging (assembly required) to ensure hassle-free installations with complete & undamaged delivery; Comprehensive assembly instructions included
- **HARDWARE INCLUDED:** The open post wall mount server rack includes a complete set of M6 square cage nuts, M6 screws and plastic washers to securely mount all of your equipment in the rack
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 15U wall mounted network rack is backed for 5-years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	5 Years
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	15U
Special Features	Adjustable Mounting Rails
	Easy Assembly
	U-Markings
	Wall-Mountable
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E
General Specifications	Internal Depth Range: 30 cm to 50.3 cm (11.8 inches to 19.8

inches)

Performance

Weight Capacity	198.4 lb [90 kg]
-----------------	------------------

Physical Characteristics

Color	Black
-------	-------

Construction Material	Steel
-----------------------	-------

Product Measurements

Product Length	20.0 in [50.8 cm]
----------------	-------------------

Product Width	19.8 in [50.4 cm]
---------------	-------------------

Product Height	30.4 in [77.3 cm]
----------------	-------------------

Weight of Product	33.6 lb [15.2 kg]
-------------------	-------------------

Maximum Mounting Depth	20.0 in [50.8 cm]
------------------------	-------------------

Packaging Information

Flat Pack (Assembly Required)	Yes
-------------------------------	-----

Package Length	21.1 in [53.7 cm]
----------------	-------------------

Package Width	32.2 in [81.7 cm]
---------------	-------------------

Package Height	5.8 in [14.7 cm]
----------------	------------------

Shipping (Package) Weight	37.0 lb [16.8 kg]
---------------------------	-------------------

What's in the Box

Included in Package	2 - Vertical Rails
	2 - Front Horizontal Brackets
	2 - Rear Horizontal Brackets
	60 - M6 Cage Nuts
	60 - M6 Screws
	60 - Plastic Washers

16 - Assembly Screws

24 - Flat Washers

24 - Bolts

1 - User Manual

**Warranty
Information**

Warranty

5 Years

**Product appearance and specifications are subject to change without notice.*