

Wall-Mount Server Rack - 2U

Product ID: RK219WALVO



The RK219WALVO 2U 19-inch Steel Side Mount Rack is a Wall Mountable Server Rack that provides a robust solution for mounting your telecom, network or server equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This 2U rack can be mounted to a wall or directly under a desk/table, expanding your workspace and keeping equipment easily accessible.

Perfect for SOHO (Small Office, Home Office) environments, the wallmount rack offers a space-saving installation for environments lacking the footprint space for a full-size server equipment rack. The rack allows your equipment to be mounted vertically - non-rackmount equipment can be installed using the rack as a wall case/chassis.

Constructed to EIA-RS310 19-inch rack standards, the RK219WALVO features a sturdy steel design and is backed by a Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Mount servers and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization
- Install a blade server anywhere in an office without a full server room

Features

- Constructed to meet the EIA-RS310 19" rack standards
- Made from solid steel for durability
- Compatible with most 19" wide rack mountable equipment
- Wall mounting holes are 16" center to center for greater stability, and mounting to standard wall studs
- Optional included 2U steel plate allows rack to be used as a wall case for any non-rackmount equipment
- TAA compliant for GSA Schedule purchases

Hardware	Warranty	Lifetime
	Wallmountable	Yes
	Rack Type	2-Post
	Frame Type	Enclosed Cabinet
	U Height	2U
	Special Features	Ships Fully Assembled
	Special Features	Wall-Mountable
	Mounting Rail Profile	L-Shape
	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
Performance	Weight Capacity	61.2 lb [27.7 kg]
Physical Characteristics	Color	Black
	Side Panel Construction	Steel
Product Measurements	Internal Width	19.6 in [5.0 cm]
	Internal Depth	18.9 in [4.8 cm]
	Product Length	4.7 in [1.2 cm]
	Product Width	19.7 in [5.0 cm]
	Product Height	21.8 in [5.5 cm]
	Weight of Product	17.7 lb [8.0 kg]
	Maximum Mounting Depth	18.9 in [4.8 cm]
Packaging Information	Flat Pack (Assembly Required)	No
		22.6 in [5.7 cm]
	Package Length	20.9 in [5.3 cm]
	Package Width	6.1 in [1.5 cm]
	Package Height	

Shipping (Package)
Weight 21.4 lb [9.7 kg]

What's in the Box	Included in Package	RK219WALVO 2U Wallmount rack
	Included in Package	#10-32 Screws
	Included in Package	#10-32 Cage Nuts

****Product appearance and specifications are subject to change without notice.***

