

## Refurbished 22U 36in Knock-Down Server Rack Cabinet with Casters

**Product ID:** RK2236BKFR



The RK2236BKFR Refurbished 22U 36in Knock-Down Server Rack Cabinet with Casters features a vented glass front door and mesh rear door that provide devices stored in the cabinet with energy and cost-efficient passive cooling.

Supporting a total load capacity of 800 kgs (1760 lbs), the server rack is constructed of steel and aluminum to provide a sturdy platform for valuable server/networking equipment. The rack is easy to assemble at the point of installation for rapid deployment and features a flat-packed design that helps minimize shipping costs.

Every refurbished server rack includes complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the paint on the metal casing, but all other components are as new. Backed by a 90-day replacement warranty.

## Certifications, Reports and Compatibility

### Applications

- Server rooms or other locations where servers and networking equipment need to be housed

### Features

- Easy assembly at the point of installation for rapid deployment
- Flat-packed design reduces handling costs
- Vented glass front door and mesh rear door for excellent passive cooling
- Front and side mounting holes to accommodate different types of equipment

---

**Hardware**

Warranty	2 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Aluminum
U Height	22U
Special Features	Grounding Lug(s) Leveling Feet U-Markings Easy Assembly Casters (Included)
Mounting Rail Profile	G-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

**Performance**

Weight Capacity (Stationary)	1768.0 lb [800.0 kg]
------------------------------	----------------------

---

**Physical Characteristics**

Color	Black
Front Door Construction	Steel with Glass/Acrylic Window
Front Door Features	Secure Key Lock with Removable Front Door
Side Panel Construction	Steel
Side Panel Features	Secure Key Lock
Rear Door Construction	Steel Mesh
Rear Door Features	Secure Key Lock with Removable Back Door

---

## Product Measurements

Internal Width	22.8 in [58 cm]
Internal Depth	39.0 in [99 cm]
Product Length	3.3 ft [1.0 m]
Product Width	23.7 in [60.3 cm]
Product Height	3.6 ft [1.1 m]
Weight of Product	138.3 lb [62.6 kg]
Maximum Mounting Depth	32.7 in [83 cm]
Minimum Mounting Depth	5.5 in [14 cm]
Product Height with Casters	3.9 ft [1.2 m]

## Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	3.9 ft [1.2 m]
Package Width	3.5 ft [1.1 m]
Package Height	11.5 in [29.2 cm]
Shipping (Package) Weight	166.4 lb [75.3 kg]

## What's in the Box

Included in Package	Adjustable Feet
	Allen Wrench
	Assembly screw kit (M4,M5,M6,M8)
	Casters
	Corner Caps
	Joints
	Left and Right Panel and frame



M6 screws and Nuts

Sets of keys.

Top and Bottom Panels

---

***\*Product appearance and specifications are subject to change without notice.***

