

## Refurbished 25U 36in Knock-Down Server Rack Cabinet with Casters

**Product ID:** RK2536BKFR



"Refurbished cabinets may have minor scratches and dents."

The RK2536BKF DuraRak 25U 36-inch (depth) server cabinet/rack features a vented acrylic front door and mesh rear door, to provide devices stored in the cabinet with cost-effective passive cooling.

Supporting a total load capacity of 815 kgs (1800 lbs), the server rack is constructed of steel and aluminum to ensure a sturdy platform for valuable server/networking equipment. The included casters make this product a flexible rack solution for any IT environment or server closet.

The rack is easy to assemble at the point of installation for rapid deployment and features a flat-packed design that helps to minimize shipping costs.

Units include complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the paint on the metal casing, but all other components are as new. Backed by a 90-day replacement warranty.

## Certifications, Reports and Compatibility



## Applications

- Perfect solution for Technology shops and repair centers with limited space and mountable equipment where security is required
- Ideal for rack mount servers, KVM switches, networking equipment and cabinet consoles
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

## Features

- Includes casters and stabilizer feet
- Flat packed into a single carton for easy shipping
- Vented doors and side panels
- Adjustable mounting rails
- Quick and easy to assemble

---

### Hardware

Warranty	Lifetime
Wallmountable	No
Rack Type	4-Post
Frame Type	Aluminum
U Height	25U
Special Features	Adjustable Mounting Rails
	Casters (Included)
	Easy Assembly
	Grounding Lug(s)
	U-Markings
Mounting Rail Profile	G-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

### Performance

Weight Capacity (Stationary)	1764.0 lb [800 kg]
------------------------------	--------------------

---

### Physical Characteristics

Color	Black
-------	-------

Front Door Construction	Steel with Glass/Acrylic Window
Front Door Features	Secure Key Lock with Reversible and Removable Front Door
Side Panel Construction	Steel
Side Panel Features	Secure Key Lock with Removable Side Panels
Rear Door Construction	Steel Mesh
Rear Door Features	Secure Key Lock with Reversible and Removable Back Door

---

#### Product Measurements

Internal Width	23.5 in [59.6 cm]
Internal Depth	39.1 in [99.2 cm]
Product Length	0.0 in [0.0 mm]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	158.8 lb [72.0 kg]
Maximum Mounting Depth	33.2 in [84.4 cm]
Minimum Mounting Depth	0.0 in [0.1 cm]
Product Height with Casters	51.4 in [130.6 cm]

---

#### Packaging Information

Flat Pack (Assembly Required)	Yes
Package Length	3.3 ft [1.0 m]
Package Width	4.3 ft [1.3 m]
Package Height	12.0 in [30.5 cm]
Shipping (Package) Weight	165.4 lb [75.0 kg]

---

#### What's in the Box

Included in Package	4 - Stabilizer feet
---------------------	---------------------

2 - Door Keys

2 - Side Panel Keys

50 - M6 Cab Screws

50 - M6 Cage Nuts

---

**Warranty  
Information**

Warranty

Lifetime

---

***\*Product appearance and specifications are subject to change without notice.***