

## 25U Server Rack Cabinet - 4 Post Adjustable Depth 7-35" Locking Vented Mobile/Rolling Network/Data/IT Equipment Enclosure w/Casters/Hook & Loop Dell PowerEdge HP ProLiant

**Product ID:** RK2537BKM



This 25U server rack provides a sleek, secure cabinet for storing standard 19" rack-mount devices such as Dell, HP, and IBM servers, along with telecommunication and A/V equipment. The rack is compatible with EIA-310 compliant equipment and supports a total load capacity of 1500 kg (3307 lb.).

This rack offers a variety of features that make it easy to install your equipment. With adjustable mounting rails, you can easily change the rail depth from 7 to 35 in. (76.2 mm - 939.8 mm) to support full-depth equipment. The added depth also provides support for additional cable and power management behind your equipment.

The rack features grommet holes on the ceiling and floor panels, which make it easy to run cabling in and out of the cabinet for discreet cable management. The rack also features grounding lugs that enable you to ground your equipment for added protection, and tool-less accessory mounting rails so you can mount 0U vertical cable managers and PDUs.

For hassle-free cable management, the rack includes a 3-meter roll of hook-and-loop cable tie that makes it easy to keep your cables tidy. You can cut the self-gripping fabric to any size, and bind your equipment cables together or to the rack.

To provide hassle-free deployment the rack ships fully assembled.

To keep your rack-mounted equipment secure, this rack features front and rear locking mesh doors that also increase airflow to provide passive cooling.

The rack also has a removable side panel with an independent quick-release lock that enables you to access your equipment easily, while still keeping it secure. Plus, a quick-release ceiling panel you can remove without interfering with cable runs that are running through your rack.

The cabinet features casters, providing ease of mobility around your office, studio or server room. Plus, the width and height of the rack fit through standard doorways, giving you the freedom to wheel your server rack into different rooms as needed.

The RK2537BKM is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Deploy in technology shops and repair centers that have limited space but tend to have mountable equipment that requires security
- Install rack-mount servers, KVM switches, networking equipment and cabinet consoles
- House rack-mount audio/video equipment for broadcasting in your editing room or television studio

### Features

- **HALF HEIGHT SECURE RACK:** 4 Post 25U 19" Server rack cabinet w/adjustable depths of up to 35", internal depth 42.3", dual panel doors for added accessibility; Locking doors & sides w/keys included
- **FULLY ASSEMBLED WITH CASTERS:** Heavy duty pre-built w/casters & levelling feet to offer maneuverability & stability; Cage nuts/screws & hook & loop tape provided so that equipment can easily be mounted
- **DESIGN AND VENTILATION:** Rolling mobile data cabinet w/strong mesh doors & vented top allow for abundant airflow & top is also removeable to run cables; 1U intervals are marked for easy identification
- **COMPATABILITY:** EIA/ECA-310-E Compliant for server/networking equipment, incl. brands like HPE ProLiant, Dell PowerEdge, and Lenovo ThinkSystem; Split rear doors reduce rear access space requirements
- **SPECS:** 5 year warranty 25U 19in free standing cabinet enclosure Mounting depth 7 to 35in. 3,315lb/1,500kg stationary capacity M6 cage nuts/screws 10ft/3m hook and loop tape Grounding lugs

---

#### Hardware

Warranty	5 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Enclosed Cabinet
U Height	25U
Special Features	Adjustable Mounting Rails
	Built-in Baying Tabs
	Built-in Cable Management



Grounding Lug(s)  
Leveling Feet  
U-Markings  
Ships Fully Assembled  
Casters (Included)

Mounting Rail Profile G-Shape  
Mounting Hole Types Square (For Cage Nut)  
Industry Standards EIA/ECA-310-E

**Performance**

Weight Capacity (Stationary) 3315.0 lb [1500 kg]

**Physical Characteristics**

Color Black  
Front Door Construction Steel Mesh  
Front Door Features Secure Key Lock with Removable Front Door  
Side Panel Construction Steel  
Side Panel Features Secure Key Lock with Removable Side Panels  
Rear Door Construction Steel Mesh  
Rear Door Features Secure Key Lock with Reversible and Removable Back Door

**Product Measurements**

Internal Width 23.7 in [60.1 cm]  
Internal Depth 3.5 ft [1.1 m]  
Product Length 3.5 ft [1.1 m]  
Product Width 23.8 in [60.4 cm]  
Product Height 3.9 ft [1.2 m]  
Weight of Product 180.8 lb [81.8 kg]



Maximum Mounting Depth 35.2 in [89.3 cm]

Minimum Mounting Depth 7.1 in [18 cm]

Product Height with Casters 4.1 ft [1.2 m]

---

**Packaging Information**

Flat Pack (Assembly Required) No

Package Length 3.8 ft [1.2 m]

Package Width 26.8 in [68.0 cm]

Package Height 4.8 ft [1.4 m]

Shipping (Package) Weight 252.6 lb [114.3 kg]

---

**What's in the Box**

Included in Package

- Server Rack Cabinet
- M6 Cage Nuts
- M6 Screws
- Plastic Cup Washers
- Keys
- Hey Key
- 10 ft. [3 m] Hook and Loop Tape
- User Manual

---

*\*Product appearance and specifications are subject to change without notice.*

