

## 4U 19in Steel Vertical Wall Mount Equipment Rack Bracket

**Product ID:** RK419WALLV



The RK419WALLV 4U Wallmount Rack Bracket offers a versatile storage solution, allowing equipment (Network devices, power strips, patch panels) to be mounted vertically (flush with the wall) to save space. Alternatively, the 4U bracket can be installed under a desk for horizontal installation, making it easy to access installed equipment directly from your workspace. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Perfect for SoHo (small office, home office) environments, the wallmount bracket offers space-saving installation for environments lacking the footprint space for a full size server equipment rack.

Suitable for mounting on virtually any wall/ceiling surface (e.g. drywall), the bracket mounting holes (used to mount to a wall or the desk underside) are positioned at exactly 16in apart, matching standard construction framework.

Constructed to EIA-310 19in rack standards, the wallmount bracket features a sturdy steel design and is backed by StarTech.com's Lifetime Warranty.

Need more storage space? StarTech.com also offers a 1U 19in Wallmount Bracket, a 2U 19in Wallmount Bracket and a 3U 19in Wallmount Bracket.

## Certifications, Reports and Compatibility

### Applications

- Mount networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Ideal for small and medium businesses needing rack solutions

## Features

- Constructed to meet the EIA-310 19" rack standards
- Made from solid steel for durability
- Arrives fully assembled with cage screws and nuts for mounting equipment
- Wall mounting holes are 16" center to center for greater stability, and mounting to standard wall studs
- Equipment can be vertically wall mounted, or horizontally under a desk
- 4U Wallmount design
- TAA compliant for GSA Schedule purchases

---

### Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	4U
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

### Performance

Weight Capacity	125.3 lb [56.7 kg]
-----------------	--------------------

---

### Special Notes / Requirements

Note	Package includes 1" screws for mounting to wood surfaces, additional hardware will be required for other materials
------	--

---

### Physical Characteristics

Color	Black
Construction Material	Steel

---



**Product Measurements**

Product Length	5.9 in [15.1 cm]
Product Width	19.8 in [50.4 cm]
Product Height	7.6 in [19.3 cm]
Weight of Product	2.4 lb [1.1 kg]

**Packaging Information**

Flat Pack (Assembly Required)	No
Package Length	20.4 in [51.9 cm]
Package Width	8.3 in [21.1 cm]
Package Height	6.4 in [16.2 cm]
Shipping (Package) Weight	3.7 lb [1.7 kg]

**What's in the Box**

Included in Package	Vertical Wall Mount Bracket
	M5 Cage Nuts
	Wood Screws
	M5 Screws
	Instruction Manual

*\*Product appearance and specifications are subject to change without notice.*

