

4U Vertical Wall-Mount Server Rack Enclosure - 18.9in deep - 2 Post - 61lb - 19in Low Profile Steel Network Equipment Cabinet

Product ID: RK419WALVO



The RK419WALVO 4U 19-inch Steel Side Mount Rack is a Wall Mountable 4U solid steel rack, providing a robust solution for mounting your telecom, network or server equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This server rack can be mounted in a server room, office, or above a doorway in rooms lacking the floor space for a full-size rack, expanding your workspace and keeping your equipment easily accessible.

The rack is constructed to EIA-RS310 standards and allows equipment to be mounted vertically - non-rackmount equipment can be installed using the rack as a wall case.

The bracket mounting holes (used to mount to a wall or the desk underside) are positioned at exactly 16-inches apart, matching standard construction stud measurements for easy installation.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Mount servers and telecommunication equipment flush against the wall
- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or retail supercenter

- Install a blade server anywhere in an office without a full server room
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization

Features

- **EASY TO USE:** This 4U wall mount rack can vertically mounted your to a wall, expanding your workspace and keeping equipment easily accessible
- **SAVES SPACE:** Perfect for SOHO environments, the wallmount network cabinet offers a space-saving installation for environments lacking the footprint space for a full-size server equipment rack
- **STURDY DESIGN:** Constructed to EIA-RS310 19-inch rack standards, the vertical wall mountable server rack features a sturdy steel design
- **TAA COMPLIANT:** This TAA compliant 4U Wall-Mount Server Rack adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this Wall-Mount Server Rack is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Enclosed Cabinet
U Height	4U
Special Features	Ships Fully Assembled
	Wall-Mountable
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	61.1 lb [27.7 kg]
-----------------	-------------------

Physical Characteristics

	Color	Black
Product Measurements		
	Internal Width	19.5 in [49.6 cm]
	Internal Depth	19.5 in [49.6 cm]
	Product Length	22.0 in [55.8 cm]
	Product Width	19.8 in [50.4 cm]
	Product Height	8.2 in [20.9 cm]
	Weight of Product	22.0 lb [10.0 kg]
	Maximum Mounting Depth	18.9 in [48 cm]
Packaging Information		
	Flat Pack (Assembly Required)	No
	Package Length	22.5 in [57.2 cm]
	Package Width	20.9 in [53.0 cm]
	Package Height	9.5 in [24.2 cm]
	Shipping (Package) Weight	26.0 lb [11.8 kg]
What's in the Box		
	Included in Package	1 - RK419WALVO 4U Wallmount Rack
		16 - #10-32 Screws
		16 - #10-32 Cage Nuts

****Product appearance and specifications are subject to change without notice.***