

Wall-Mount Server Rack with Dual Fans and Lock - 4U

Product ID: RK419WALVS



The RK419WALVS 4U 19-inch Secure Wall Mountable Server Rack is a lockable, solid steel storage rack that provides a robust solution for wall mounting telecom, network or server equipment, and includes two 120mm fans, for improved airflow. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This 4U rack can be mounted to a wall in a server room, office, or above a doorway in rooms lacking the space for a full-size rack, to expand your workspace and keep your equipment protected from unauthorized access.

Constructed to EIA-RS310 standards, the server rack allows equipment to be mounted horizontally, and offers a hinged lockable front cover as well as a lockable body. Alternatively, non-rackmount equipment can be mounted vertically with the included bottom cover, using the rack as a wall case.

The bracket mounting holes (used to mount to a wall or desk) are positioned at 16-inches apart, matching standard stud measurements for easy installation.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Securely mount servers and telecommunication equipment flush against the wall
- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or retail supercenter
- Install a large server anywhere in an office without a full server room, while protecting against unauthorized access

- Ideal for small and medium businesses requiring small, secure rack solutions dispersed throughout the organization

Features

- Includes optional 4U steel plate which acts as a shelf, allowing the rack to be used as a wall case for any non-rackmount equipment
- Hinged, lockable front cover
- TAA compliant for GSA Schedule purchases
- Both the top cover and the rack body are lockable separately for varying security levels
- 2 x 120mm fans included
- Wall mounting holes are 16" center to center for greater stability, and mounting to standard wall studs
- Compatible with most 19in wide rack-mountable equipment
- Solid steel construction
- Constructed to meet the EIA-RS310 19in rack standards

Power

Warranty	Lifetime
Input Voltage	115V DC
Plug Type	NEMA 1-15 Power (North America) Plug

Physical Characteristics

Color	Black
Material	Steel
Product Length	28.5 in [72.5 cm]
Product Width	25.4 in [64.4 cm]
Product Height	8.6 in [21.9 cm]
Weight of Product	44.0 lb [19.9 kg]

Packaging Information

Package Length	30.5 in [77.4 cm]
----------------	-------------------



Package Width	28.0 in [71.0 cm]
Package Height	11.3 in [28.8 cm]
Shipping (Package) Weight	51.0 lb [23.1 kg]

What's in the Box

Included in Package	RK419WALVS 4U Wallmount rack
	Set of Keys
	#10-32 Panel Screws
	#10-32 Cage Nuts

****Product appearance and specifications are subject to change without notice.***

