

Refurbished 4U 19in Secure Horizontal Wall Server Rack with 2 Fans

Product ID: RK419WALVSR



The RK419WALVSR Refurbished 4U 19-inch Secure Horizontal Wall Mountable Server Rack is a lockable, solid steel storage rack that provides a robust solution for wall mounting telecom, network or server equipment, and includes two 120mm fans, for improved airflow.

This 4U rack can be mounted to a wall in a server room, office, or above a doorway in rooms lacking the space for a full-size rack, to expand your workspace and keep your equipment protected from unauthorized access.

Constructed to EIA-RS310 standards, the server rack allows equipment to be mounted horizontally, and offers a hinged lockable front cover as well as a lockable body. Alternatively, non-rackmount equipment can be mounted vertically with the included bottom cover, using the rack as a wall case.

The bracket mounting holes (used to mount to a wall or desk) are positioned at 16-inches apart, matching standard stud measurements for easy installation.

Every refurbished server rack includes complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the paint on the metal casing, but all other components are as new. Backed by a 90-day replacement warranty,.

Certifications, Reports and Compatibility



Applications

- Securely mount servers and telecommunication equipment flush against the wall

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or retail supercenter
- Install a large server anywhere in an office without a full server room, while protecting against unauthorized access
- Ideal for small and medium businesses requiring small, secure rack solutions dispersed throughout the organization

Features

- Includes optional 4U steel plate which acts as a shelf, allowing the rack to be used as a wall case for any non-rackmount equipment
- Hinged, lockable front cover
- Both the top cover and the rack body are lockable separately for varying security levels
- 2 x 120mm fans included
- Wall mounting holes are 16" center to center for greater stability, and mounting to standard wall studs
- Compatible with most 19in wide rack-mountable equipment
- Solid steel construction
- Constructed to meet the EIA-RS310 19in rack standards

Hardware

Warranty	None
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Steel
U Height	4U
Special Features	Grounding Lug(s)
	Lockable Top Hatch
	Ships Fully Assembled
	Wall-Mountable
Mounting Rail Profile	L-Shape
Fan Options	Two Fans Included: 120 mm

	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
Performance		
	Airflow Rate	106 CFM
	Audible Noise	46 dBA @ 1 Meter
	Weight Capacity	149.9 lb [68 kg]
Physical Characteristics		
	Color	Black
	Front Door Construction	Steel
	Front Door Features	Secure Key Lock with Removable Front Door
	Side Panel Construction	Steel
Product Measurements		
	Internal Width	25.2 in [64.1 cm]
	Internal Depth	28.4 in [72.1 cm]
	Product Length	28.5 in [72.5 cm]
	Product Width	25.4 in [64.4 cm]
	Product Height	8.6 in [21.9 cm]
	Weight of Product	43.9 lb [19.9 kg]
	Maximum Mounting Depth	21.8 in [55.3 cm]
Packaging Information		
	Flat Pack (Assembly Required)	No
	Package Length	30.5 in [77.4 cm]
	Package Width	28.0 in [71.0 cm]
	Package Height	11.3 in [28.8 cm]
	Shipping (Package)	50.9 lb [23.1 kg]

Weight

What's in the Box

Included in Package	1 - RK419WALVSR 4U Wallmount rack
	1 - Set of Keys
	24 - #10-32 Panel Screws

****Product appearance and specifications are subject to change without notice.***