

42U Rack Enclosure Server Cabinet - 29.9 in. Deep

Product ID: RK4236BK



The RK4236BK 42U 36in Server Rack Cabinet with Steel Mesh Door provides excellent quality at an affordable price, while an innovative split rear door design helps save space in the server room.

The 42U 36in Server Cabinet includes an integrated cable management system that simplifies planning and installing rackmount equipment with clearly marked rail spacing. Plus, adjustable front and rear rails allow you to shift mounting depths to suit almost any piece of rackmount equipment.

StarTech.com's RK line of DuraRak cabinets are modular, designed to suit any server room footprint design. The RK4236BK is also available in an open rack design (RK4236BKNS), so that several cabinets can be joined together using only 2 side panels - saving cost and increasing passive airflow.

Backed by a StarTech.com Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

Features

- Split rear door minimizes the required access space behind the cabinet
- Includes lockable front and rear doors

- Includes integrated cable management system
- Front and rear doors easily removable and reversible
- All steel, welded frame construction
- Ships fully assembled
- Hassle-free side access to mounted equipment with lightweight, 3-piece side panels

Hardware

Warranty	Lifetime
Wallmountable	No
Rack Type	4-Post
Frame Type	Steel (2mm)
U Height	42U
Special Features	Ships Fully Assembled Casters (Included)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity (Stationary)	2210.0 lb [1000 kg]
------------------------------	---------------------

Physical Characteristics

Color	Black
Front Door Construction	Steel Mesh
Front Door Features	Secure Key Lock
Side Panel Construction	Steel
Rear Door Construction	Steel Mesh

Product Measurements

Internal Width	18.3 in [46.5 cm]
Internal Depth	28.0 in [71.1 cm]



Product Length	0.0 in [0.0 mm]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	289.5 lb [131.0 kg]
Maximum Mounting Depth	29.9 in [76 cm]
Product Height with Casters	6.6 ft [2.0 m]

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	26.4 in [67.0 cm]
Package Width	38.2 in [97.0 cm]
Package Height	6.6 ft [2.0 m]
Shipping (Package) Weight	311.6 lb [141.0 kg]

What's in the Box

Included in Package	42U 36" DuraRak
	Allen key for skid removal
	Cable access caps
	Integrated cable management system
	Leveling feet
	Package of mounting screws
	Set of keys for doors and sides

****Product appearance and specifications are subject to change without notice.***

