

## 42U Rack Enclosure Server Cabinet - 29.9 in. Deep

**Product ID:** RK4236BK



The RK4236BK 42U 36in Server Rack Cabinet with Steel Mesh Door provides excellent quality at an affordable price, while an innovative split rear door design helps save space in the server room.

The 42U 36in Server Cabinet includes an integrated cable management system that simplifies planning and installing rackmount equipment with clearly marked rail spacing. Plus, adjustable front and rear rails allow you to shift mounting depths to suit almost any piece of rackmount equipment.

StarTech.com's RK line of DuraRak cabinets are modular, designed to suit any server room footprint design. The RK4236BK is also available in an open rack design (RK4236BKNS), so that several cabinets can be joined together using only 2 side panels - saving cost and increasing passive airflow.

Backed by a StarTech.com Lifetime Warranty.

## Certifications, Reports and Compatibility



## Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

## Features

- Includes lockable front and rear doors
- Split rear door minimizes the required access space behind the cabinet
- Hassle-free side access to mounted equipment with lightweight, 3-piece side panels
- Front and rear doors easily removable and reversible
- Includes integrated cable management system
- All steel, welded frame construction
- Ships fully assembled

---

#### Hardware

Warranty	Lifetime
Wallmountable	No
Rack Type	4-Post
Frame Type	Steel (2mm)
U Height	42U
Special Features	Casters (Included)
	Ships Fully Assembled
Industry Standards	EIA/ECA-310-E

---

#### Performance

Weight Capacity (Stationary)	2205.0 lb [1000 kg]
------------------------------	---------------------

---

#### Physical Characteristics

Color	Black
Front Door Construction	Steel Mesh
Front Door Features	Secure Key Lock
Side Panel Construction	Steel
Rear Door Construction	Steel Mesh

---

#### Product Measurements

Internal Width	18.3 in [46.5 cm]
Internal Depth	28.0 in [71.1 cm]
Product Length	0.0 in [0.0 cm]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	4624.3 oz [131000.0 g]
Maximum Mounting Depth	29.9 in [76 cm]
Product Height with Casters	78.7 in [199.8 cm]

---

#### Packaging Information

Flat Pack (Assembly Required)	No
Package Length	26.4 in [67.0 cm]
Package Width	38.2 in [97.0 cm]
Package Height	6.6 ft [2.0 m]
Shipping (Package) Weight	310.9 lb [141.0 kg]

---

#### What's in the Box

Included in Package	1 - 42U 36" DuraRak
	1 - Integrated cable management system
	4 - Leveling feet
	4 - Cable access caps
	1 - Allen key for skid removal
	1 - Set of keys for doors and sides
	1 - Package of mounting screws

---

***\*Product appearance and specifications are subject to change without notice.***