

42U Rack Enclosure Server Cabinet - 36.6 in. Deep

Product ID: RK4242BK



The RK4242BK 42U 42in Server Rack Cabinet features an all steel, welded frame construction that provides durable, high quality rack storage at an affordable price.

This modular 42U cabinet helps save space in the server room by using an innovative split rear door, and is designed to suit any server room footprint design, while housing any standard 19in rackmount equipment. Plus, adjustable front and rear rails allow you to shift mounting depths to suit almost any piece of rackmount equipment.

To help optimize ventilation, the cabinet offers steel mesh doors with wide perforation, and includes an integrated cable management system that helps keep the inside of the cabinet neat. Plus, the rack rail spacing is clearly marked, making it easy to plan and install equipment within the cabinet.

This high quality 42U Server Rack Cabinet is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

Features

- Extra deep 42" enclosure accommodates all full size rackmount equipment
- Includes lockable front and rear doors
- Hassle-free side access to mounted equipment with lightweight, 3-piece side panels
- Split rear door minimizes the required access space behind the cabinet
- Includes integrated cable management system, casters, leveling feet, mounting screws
- Front and rear doors easily removable
- All steel, welded frame construction
- Ships fully assembled

Hardware

Warranty	Lifetime
Wallmountable	No
Rack Type	4-Post
Frame Type	Aluminum
U Height	42U
Special Features	Adjustable Mounting Rails
	Casters (Included)
	Grounding Lug(s)
	Ships Fully Assembled
	U-Markings
Mounting Rail Profile	G-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity (Stationary)	2205.0 lb [1000 kg]
------------------------------	---------------------

Physical Characteristics

Color	Black
Front Door Construction	Steel Mesh
Front Door Features	Secure Key Lock
Side Panel Construction	Steel
Side Panel Features	Removable Side Panels
Rear Door Construction	Steel Mesh
Rear Door Features	Secure Key Lock

Product Measurements

Internal Width	23.7 in [60.2 cm]
Internal Depth	42.2 in [107.1 cm]
Product Length	44.7 in [113.5 cm]
Product Width	24.0 in [61 cm]
Product Height	77.4 in [196.6 cm]
Weight of Product	342.1 lb [155.1 kg]
Maximum Mounting Depth	35.6 in [90.5 cm]
Minimum Mounting Depth	0.4 in [1.1 cm]
Product Height with Casters	80.2 in [203.7 cm]

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	3.8 ft [1.2 m]
Package Width	26.4 in [67 cm]
Package Height	7.4 ft [2.3 m]
Shipping (Package) Weight	358.1 lb [162.4 kg]

What's in the Box

Included in Package	1 - 42U 42" DuraRak
	1 - Integrated cable management system
	4 - Leveling feet
	4 - Cable access caps
	1 - Allen key for skid removal
	1 - Set of keys for doors and sides
	40 - M5 Screws
	40 - M5 Cage Nuts

**Warranty
Information**

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***