

42U 42in Server Rack Cabinet (no Sides)

Product ID: RK4242BKNS



The RK4242BKNS 42U 42in Server Rack Cabinet (No Sides) features an all steel, welded frame construction that provides durable, high quality rack storage at an affordable price.

This modular 42U cabinet helps save space in the server room by using an innovative split rear door, and is designed to suit any server room footprint design, while housing any standard 19in rackmount equipment. To simplify planning and equipment installation, the rack includes an integrated cable management system and clearly marked rail spacing. Plus, adjustable front and rear rails allow you to shift mounting depths to suit almost any piece of rackmount equipment.

The RK4242BKNS is also available as an enclosed rack (RK4242BK) so that several cabinets can be joined together using only 2 side panels, saving cost and increasing passive airflow.

Backed by a StarTech.com Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

Features

- Split rear door minimizes the required access space behind the cabinet
- Extra deep 42" enclosure accommodates all full size rackmount equipment

- Front and rear doors are easily removable and can be reversed
- Includes integrated cable management system
- Lockable front and rear doors
- Ships fully assembled
- All steel, welded frame construction

Hardware

Warranty	Lifetime
Wallmountable	No
Frame Type	Steel (2mm)
U Height	42U
Front Door Construction	Steel Mesh
Rear Door Construction	Steel Mesh
Fan(s)	No
Casters	Included
Industry Standards	EIA RS310-D

Performance

Weight Capacity (Stationary)	2210.0 lb [1000 kg]
------------------------------	---------------------

Physical Characteristics

Color	Black
Internal Width	18.3 in [46.5 cm]
Internal Depth	34.0 in [86.4 cm]
Product Length	3.5 ft [1.1 m]
Product Width	23.8 in [60.5 cm]
Product Height	6.5 ft [2.0 m]
Weight of Product	221.0 lb [100 kg]

Product Height with Casters	6.6 ft [2.0 m]
-----------------------------	----------------

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	3.7 ft [1.1 m]
Package Width	26.0 in [66 cm]
Package Height	6.6 ft [2.0 m]
Shipping (Package) Weight	245.3 lb [111 kg]

What's in the Box

Included in Package	42U 42" DuraRak Rack
	Allen key for skid removal
	Cable access caps
	Integrated cable management system
	Leveling feet
	Package of mounting screws
	Set of keys for doors

****Product appearance and specifications are subject to change without notice.***

