

## Refurbished 42U 42in Server Rack Cabinet

**Product ID:** RK4242BKR



The RK4242BKR Refurbished 42U 42in Server Rack Cabinet features an all steel, welded frame construction that provides durable, high quality rack storage at an affordable price.

This modular 42U cabinet helps save space in the server room by using an innovative split rear door, and is designed to suit any server room footprint design, while housing any standard 19in rackmount equipment.

To help optimize ventilation, the cabinet offers steel mesh doors with wide perforation, and includes an integrated cable management system that helps keep the inside of the cabinet neat. Plus, the rack rail spacing is clearly marked, making it easy to plan and install equipment within the cabinet.

Units include complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the paint on the metal casing, but all other components are as new. Backed by a 90-day replacement warranty.

## Certifications, Reports and Compatibility



## Applications

- Ideal for rack mount servers, KVM switches, networking equipment and cabinet consoles

## Features

- Split rear door minimizes the required access space behind the cabinet

- Includes integrated cable management system, casters, leveling feet, mounting screws
- Ships fully assembled
- All steel, welded frame construction
- Front and rear doors easily removable
- Includes lockable front and rear doors, and dual lock side panels
- Extra deep 42" enclosure accomodates all full size rackmount equipment
- Lifetime warranty

---

#### Hardware

Warranty	None
Wallmountable	No
Rack Type	4-Post
Frame Type	Steel (2mm)
U Height	42U
Special Features	Adjustable Mounting Rails
	Casters (Included)
	Grounding Lug(s)
	Ships Fully Assembled
	U-Markings
Mounting Rail Profile	G-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

#### Performance

Weight Capacity (Stationary)	2205.0 lb [1000 kg]
------------------------------	---------------------

---

#### Physical Characteristics

Color	Black
-------	-------

Front Door Construction	Steel Mesh
Front Door Features	Secure Key Lock
Side Panel Construction	Steel
Side Panel Features	Removable Side Panels
Rear Door Construction	Steel Mesh
Rear Door Features	Secure Key Lock

---

#### Product Measurements

Internal Width	23.7 in [60.2 cm]
Internal Depth	42.2 in [107.1 cm]
Product Length	3.7 ft [1.1 m]
Product Width	24.0 in [61.0 cm]
Product Height	77.4 in [196.6 cm]
Weight of Product	342.1 lb [155.1 kg]
Maximum Mounting Depth	35.6 in [90.5 cm]
Minimum Mounting Depth	0.4 in [1.1 cm]
Product Height with Casters	80.2 in [203.7 cm]

---

#### Packaging Information

Flat Pack (Assembly Required)	No
Package Length	3.8 ft [1.2 m]
Package Width	26.4 in [67.0 cm]
Package Height	7.4 ft [2.3 m]
Shipping (Package) Weight	358.1 lb [162.4 kg]

---

#### What's in the Box

Included in Package	1 - 42U 42" DuraRak
---------------------	---------------------

2 - 42" Enclosure sides (installed)

1 - Integrated cable management system

4 - Leveling feet

4 - Cable access caps

1 - Allen key for skid removal

1 - Set of keys for doors and sides

1 - Package of mounting screws

---

**Warranty  
Information**

Warranty

Refurbished 90 Days

---

***\*Product appearance and specifications are subject to change without notice.***