

2 Post 6U 19" Wall Mount Network Cabinet - 15" Deep Locking IT Switch Depth Enclosure - Vented Computer/Electronics Equipment Data Rack w/Shelf & Hook & Loop Tape /Assembled

Product ID: RK616WALM



This 6U server rack cabinet lets you mount your EIA-310 compliant equipment to the wall. The enclosure features a mounting depth up to 15 in. and offers a maximum load capacity of 200 lb. (90 kg).

Save valuable floor space, by wall-mounting the enclosure. The wall-mounted design makes this enclosure the ideal solution for optimizing equipment storage in your classroom, retail store, server room or office. This rack also includes a 1U shelf that gives you a stable surface for storing your tools or placing equipment that's not rack-mountable.

The wall-mount network rack makes it easy to install your equipment, with 2-post mounting rails that can be positioned to create more room at the front or the back of the enclosure depending on your requirements.

The 6U network cabinet features a removable and reversible front door and removable side panels, each with quick-release mechanisms, so you can easily access your equipment. Plus, each door and panel on this rack features an independent lock, ensuring your equipment is secure. The wall-mount server rack also includes all of the cage nuts and mounting screws you'll need to fill the rack with equipment, saving you the time, hassle and cost of sourcing mounting hardware.

For hassle-free cable management, the rack includes a 3-meter roll of hook-and-loop cable tie that makes it easy to keep your cables neat and tidy by binding them together or binding them to the rack. The self-gripping fabric can be cut to any size, enabling a wrap-around solution for the cables of any rack-mount equipment.

This server rack enclosure features heavy-duty steel construction, with lockable doors at all entrances. For hassle-free equipment installation, the mounting rails on the rack can be switched for use with square holes and cage nuts, or tapped rails.

To ensure your equipment is running at an optimal temperature, the server rack/cabinet promotes passive cooling. It features mesh doors and vented top and bottom panels for maximum airflow.

For simple and sturdy mounting, the rack's mounting holes are positioned 16 in. apart, so you can securely attach it to a wall using wall studs.

The RK616WALM is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Wall-mount your server and networking equipment flush against the wall, in areas with limited space, such as technology store fronts or repair centers
- Install the rack in your small office environment, where you can't fit a full-sized rack
- Organize cabling or equipment in your network closet, wiring closet, back office or IDF

Features

- **6U 2 POST SECURE RACK:** This locking wall mount network cabinet enclosure is designed to protect critical network equipment from damage and is lockable to prevent unauthorized access
- **DURABLE:** This SPCC cold rolled steel data/network equipment cabinet holds up to 200 lb (90 kg) and can support depth of 14.6in and comes with a movable vented 1U shelf
- **SPECS:** 6U 19" Enclosed cabinet 2 Post EIA/ECA-310-E compliant Mounting depth 14.6 in. 200 lb (90 kg) capacity Lockable door & sides 1U vented shelf included 5 year warranty
- **DESIGNED FOR COOLING:** The door and sides are a strong mesh that improves airflow around devices, and if additional cooling needed, up to four optional 120mm fans can be installed for active cooling
- **PRE-ASSEMBLED:** This rack is pre-assembled and ready to be installed. Includes cage nuts and screws, 4 security keys, grounding lugs, and 3m of Hook-and-Loop tape to keep cables organized and secure

Hardware

Warranty	5 Years
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Enclosed Cabinet
U Height	6U
Special Features	Adjustable Mounting Rails
	Built-in Cable Management
	Grounding Lug(s)

	U-Markings
	Wall-Mountable with Rear Access Hinges
	Ships Fully Assembled
Mounting Rail Profile	L-Shape
Fan Options	Four Optional Fans: 120 mm
Mounting Hole Types	Square (For Cage Nut)
	Threaded Hole
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	198.9 lb [90 kg]
-----------------	------------------

Special Notes / Requirements

Note	Includes CABSHELFV1U and 2 pairs of keys
------	--

Physical Characteristics

Color	Black
Front Door Construction	Steel Mesh
Front Door Features	Secure Key Lock with Reversible and Removable Front Door
Side Panel Construction	Steel Mesh
Side Panel Features	Secure Key Lock with Removable Side Panels

Product Measurements

Internal Width	23.4 in [59.4 cm]
Internal Depth	17.7 in [45 cm]
Product Length	17.7 in [45 cm]
Product Width	23.6 in [60 cm]
Product Height	14.6 in [37.1 cm]
Weight of Product	38.9 lb [17.6 kg]



Maximum Mounting Depth	14.8 in [37.5 cm]
------------------------	-------------------

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	26.6 in [67.5 cm]
Package Width	20.7 in [52.5 cm]
Package Height	17.7 in [45 cm]
Shipping (Package) Weight	43.3 lb [19.6 kg]

What's in the Box

Included in Package	wall-mount enclosure
	1U shelf
	roll of hook-and-loop fastener
	12-24 cage nuts
	12-24 screws
	door keys
	side panel keys
	instruction manual

****Product appearance and specifications are subject to change without notice.***

