

6U 19in Wallmount Server Rack Cabinet with Acrylic Door

Product ID: RK619WALLGB



The RK619WALLGB Wall-Mounted 6U Server Rack/Cabinet can be fastened to most types of walls and features a sturdy, compact design that can be positioned almost anywhere, without wasting valuable floor space. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

This equipment rack offers 6U of storage space and is designed to accommodate 19-inch (wide) servers, networking and telecom equipment. The rack features a 12cm fan, with ventilation positioned above and below the front panel glass door, helping to keep dust out of the rack while ensuring a cool operating environment for your valuable equipment.

To ensure optimum security and prevent tampering with the enclosed equipment, the cabinet/rack features a lockable, smoked acrylic front door that can be removed entirely or installed to open to the left or right as needed.

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility

Applications

- Mount networking and telecommunication equipment to the wall
- Securely protect and wall mount sensitive rackmountable equipment
- Install rack equipment over doorways, or in tight spaces (e.g. server closets)

Features

- Compact wallmount design and rugged steel construction
- Vented panels with a 120mm cooling fan
- Lockable acrylic door with a large viewing area
- Large side and bottom cable routing holes with grommets
- TAA compliant for GSA Schedule purchases

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Steel
U Height	6U
Special Features	Ships Fully Assembled Wall-Mountable
Mounting Rail Profile	L-Shape
Fan Options	One Fan Included: 120 mm + One Optional Fan: 120 mm
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	110.5 lb [50 kg]
-----------------	------------------

Physical Characteristics

Color	Black
Front Door Construction	Steel with Glass/Acrylic Window
Front Door Features	Secure Key Lock
Side Panel Construction	Steel

Product Measurements



Internal Width	17.8 in [45.1 cm]
Internal Depth	14.7 in [37.5 cm]
Product Length	0.0 in [0 mm]
Product Width	0.0 in [0 mm]
Product Height	0.0 in [0 mm]
Weight of Product	22.9 lb [10.4 kg]
Maximum Mounting Depth	11.2 in [28.6 cm]

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	27.0 in [68.5 cm]
Package Width	18.3 in [46.5 cm]
Package Height	18.4 in [46.8 cm]
Shipping (Package) Weight	29.3 lb [13.3 kg]

What's in the Box

Included in Package	6U Wallmount Cabinet
	Set of keys
	Pack of CAB screws and Cage nuts(20 each)
	UK to EU plug converter
	M5 Screws
	M5 Cage Nuts

****Product appearance and specifications are subject to change without notice.***

