

8U 19" Wall Mount Network Rack - Adjustable Depth 12-20" 2 Post Open Frame Server Room Rack for AV/Data/ IT Communication/Computer Equipment/Switch w/Cage Nuts & Screws

Product ID: RK812WALLOA



The RK812WALLOA 8U Open Frame Wall Mount Equipment Rack with Adjustable Depth is a high-quality, sturdy relay rack solution that is easy to assemble and install into any environment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The open rack features an adjustable depth ranging from 12-20 inches, in order to accommodate larger data, network and telecommunications devices. The greater than average depth of the rack also allows for mounting of shelves and other accessories. The wall mounts are positioned 16in apart (center to center), making it suitable for mounting on virtually any wall surface, based on North American wall frame stud spacing standards.

This 8U rack can be mounted to the wall in a server room, office, or above a doorway, expanding your workspace and keeping your equipment easily accessible.

Backed by a StarTech.com lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location
- Mount Audio/Video broadcast or distribution components
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization

Features

- **LIFETIME WARRANTY:** StarTech.com offers 24 hour technical support and has been the choice of IT professionals for 30 years, conducting thorough compatibility and performance testing on all our products
- **ACCESSORIES INCLUDED:** The wall mount server room/ computer/communication/AV/IT equipment rack includes a complete set of 16 screws & cage nuts to securely mount all of your equipment in the rack
- **HEAVY DUTY:** Heavy duty 2 post open frame rack supports unobstructed airflow and is easy to install with a durable design made from SPCC cold-rolled steel with support for up to 135lbs of equipment
- **DURABLE & ADJUSTABLE:** This adjustable 8U 19" open frame wall mount network rack is EIA/ECA-310 compatible w/ 12-20" mounting depth supports most network switches like Cisco 2960
- **CERTIFIED PACKAGING:** The rack ships flat packed with ISTA-6 certified packaging to ensure complete and undamaged delivery and also features comprehensive assembly instructions

Hardware	Warranty	Lifetime
	Wallmountable	Yes
	Rack Type	2-Post
	Frame Type	Open Frame
	U Height	8U
	Special Features	Ships Fully Assembled
	Special Features	Wall-Mountable
	Mounting Rail Profile	G-Shape
	Mounting Hole Types	Square (For Cage Nut)
	Industry Standards	EIA/ECA-310-E
Performance	Weight Capacity	135.3 lb [61.2 kg]
Special Notes / Requirements	Note	Hardware to mount the rack to the wall is not provided
Physical Characteristics	Color	Black
	Construction Material	Steel
Product Measurements	Product Length	12.0 in [3.0 cm]
	Product Width	19.8 in [5.0 cm]
	Product Height	17.9 in [4.6 cm]
	Weight of Product	24.4 lb [11.1 kg]
	Maximum Mounting Depth	19.7 in [5 cm]
Packaging Information	Flat Pack (Assembly Required)	No
	Package Length	21.9 in [5.6 cm]

Package Width	13.8 in [3.5 cm]
Package Height	19.3 in [4.9 cm]
Shipping (Package) Weight	28.8 lb [13.0 kg]

What's in the Box	Included in Package	Wall Mount Rack
	Included in Package	Assembly Screws
	Included in Package	M5 Screws
	Included in Package	M5 Cage Nuts
	Included in Package	Truss Head Screws
	Included in Package	Installation Guide

****Product appearance and specifications are subject to change without notice.***

