

8U Sideways Wall-Mount Rack for Servers

Produkt ID: RK819SIDEM



The RK819SIDEM Side-mounted Wallmount Open Frame Rack/Cabinet is an 8U server rack that lets you mount your (19-inch wide) servers, A/V or network equipment facing perpendicular to the wall, for easy access to mounted devices and equipment. The cabinet/rack features open access to both the front and back of your devices, making it easy to adjust cabling, view LEDs and access configuration buttons as needed. Plus, the nature of the sidemount configuration allows for deeper mounting depths than typical wallmount racks, without causing an obstruction. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Constructed of high-quality SPCC cold-rolled steel, for strength and durability, the open frame equipment rack allows for maximum airflow while still supporting a maximum weight capacity of 159 kg (350 lbs). The wall mount rack also ships complete with all of the M5 screws and cage nuts required to mount your equipment, saving the expense of purchasing them separately.

Backed by a StarTech.com Lifetime warranty.

Certifikat, rapporter och kompatibilitet



Användning

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location

- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization
- Mount Audio/Video broadcast or distribution components

Funktioner

- Ships fully assembled and includes all necessary screws/nuts
- TAA compliant for GSA Schedule purchases
- Weight capacity of 350 lb (159 kg)
- Sidemount configuration allows for a greater mounting depth
- Sturdy SPCC cold-rolled steel construction
- Open frame design for optimum airflow
- Wall mount holes are 16" center-to-center, for mounting to any standard wooden studs (easily mounts to concrete or steel as well)

Hårdvara

Garantipolicy	Lifetime
Väggmonterbar	Ja
Hylltyp	4 stag
Ramtyp	Öppen ram
U-höjd	8U
Specialfunktioner	Ships Fully Assembled Kan monteras på väggen
Profil monteringsskenor	L-Shape
Mounting Hole Types	Kvadrat (för burmutter)
Industristandarder	EIA/ECA-310-E

Prestanda

Weight Capacity	350.6 lb [159 kg]
-----------------	-------------------

Utseende		
	Färg	Svart
	Construction Material	Stål
Product Measurements		
	Produktlängd	22.2 in [56.5 cm]
	Produktbredd	21.2 in [53.8 cm]
	Produkthöjd	19.0 in [48.3 cm]
	Produktvikt	39.8 lb [18.0 kg]
	Maximalt monteringsdjup	20.8 in [52.9 cm]
Förpackning		
	Platt paket (montering krävs)	Nej
	Paketets längd	23.5 in [59.6 cm]
	Paketets bredd	22.7 in [57.6 cm]
	Paketets höjd	20.4 in [51.7 cm]
	Fraktvikt (förpackning)	46.3 lb [21.0 kg]
Vad det är i lådan		
	Ingår i paketet	1 - 8U Rack
		36 - M5 Screws
		36 - M5 Cage Nuts
Warranty Information		
	Warranty	Livslängd

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.