

## 8U Hinged Open Frame Wall-Mount Server Rack - 22 in. Deep

**Product ID:** RK819WALLOH



The RK819WALLOH 8U 22in Depth Hinged Open Frame Wall Mount Server Rack lets you wall mount your (19-inch wide) servers, A/V or network equipment and features a hinged rack design that allows the entire frame to swing open for easy installation and maintenance of your equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The 8U wallmount rack offers a 4 post design for additional support of your equipment, storing a maximum weight capacity of 63 kg (140 lbs). Constructed of high-quality SPCC cold-rolled steel for strength and durability, the open frame wallmount server rack allows for maximum airflow, and ships complete with all of the rack screws and cage nuts required to mount your equipment, saving the expense of purchasing them separately.

Backed by a StarTech.com Lifetime warranty.

### **Certifications, Reports and Compatibility**

#### **Applications**

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization
- Mount Audio/Video broadcast or distribution components

#### **Features**

- 8U Hinged Wall Mount Rack

- Hinged design for easy access to rear panels
- Open frame design provides additional airflow
- Package includes all necessary screws/nuts for mounting rack equipment
- Sturdy SPCC cold-rolled steel construction
- 4 Post design for added stability
- TAA compliant for GSA Schedule purchases

---

#### Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	4-Post
Frame Type	Open Frame
U Height	8U
Special Features	Ships Fully Assembled Wall-Mountable
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

#### Performance

Weight Capacity	140.0 lb [63.4 kg]
-----------------	--------------------

---

#### Physical Characteristics

Color	Black
Construction Material	Steel

---

#### Product Measurements

Product Length	23.7 in [60.3 cm]
Product Width	21.9 in [55.5 cm]
Product Height	19.2 in [48.8 cm]



Weight of Product	33.3 lb [15.1 kg]
Maximum Mounting Depth	19.8 in [50.2 cm]

---

**Packaging Information**

Flat Pack (Assembly Required)	No
Package Length	26.0 in [66 cm]
Package Width	25.0 in [63.5 cm]
Package Height	21.6 in [54.8 cm]
Shipping (Package) Weight	39.1 lb [17.7 kg]

---

**What's in the Box**

Included in Package	Hinged Wall Mount Rack
	#10-32 Screws
	#10-32 Cage Nuts
	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

