

## 8U 19" Vertical Wall Mount Server Rack Cabinet - Low Profile (15") - 30" Deep Locking Network Enclosure w/2U for Switch Patch Panel Router Mounting IT/Data Cabinet Assembled

Product ID: RK830WALVS



This 8U vertical server cabinet offers a space-saving way to keep your network and server equipment secure. With its 30 in. depth, and a weight capacity of up to 200 lb. (90.7 kg), the server rack/cabinet is designed to fit your needs. It also features an additional 2U mounting bracket positioned toward the top of the enclosure, that you can use to mount patch cables or other shallow rack-mount equipment.

Wall-mount your equipment, even if you don't have enough space for a full-sized rack or cabinet. This low-profile server cabinet is perfect for areas where space is at a premium, such as an office. The cabinet saves space by extending only minimally from the wall and housing the length of your equipment vertically. This reduces the horizontal footprint of your equipment while still providing plenty of room for your servers, patch panels, and switches.

To help keep your equipment secure, the vertical server cabinet/network rack features a sturdy metal design and a lock on both the door and access panel. It is also vented, providing passive cooling to help keep your equipment running at suitable temperatures.

The server rack comes fully assembled and includes all of the necessary hardware to install equipment, making installation fast and easy. The mounting holes are spaced 16 in. apart, making it suitable for mounting on almost any wall, based on common North American wall-frame stud spacing.

The RK830WALVS is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Securely mount servers and telecommunication equipment flush against the wall
- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or retail supercenter
- Install a large server anywhere in an office, without a full server room, while protecting against unauthorized access
- Ideal for small and medium businesses requiring small, secure rack solutions dispersed throughout the organization

## Features

- **MOUNT YOUR SERVERS VERTICALLY:** This 8U vertical wall mount server rack cabinet features a space saving low profile design & provides up to 30" of mounting depth while only extending 15" from the wall
- **INCLUDES AN EXTRA 2U OF MOUNTING SPACE:** 2U of angled 2 post horizontal mounting space is provided above the vertical server mounting rails for switches, patch panels, and routers up to 4.7" in depth
- **TECH SPECS:** 8U 19" Vertical Wallmount Enclosure Pre-Assembled EIA/ECA-310-E Rear & Bottom Cable Routing 200 lb (90 kg) Weight Capacity Mounting Screws Incl. Optional 2x 120mm Fans
- **MULTIPLE SECURITY FEATURES:** Locking side panels w/ 4 keys, for multiple levels of security; cabling can routed into the cabinet from the wall without exposing cables for extra security
- **STARTECH.COM ADVANTAGE:** IT professionals choice for over 30 years; this vertical wallmount network/data rack is backed for 5 years by StarTech.com, includes free 24/5 North America based tech support

<b>Hardware</b>	Warranty	5 Years
	Wallmountable	Yes
	Rack Type	2-Post
	Frame Type	Enclosed Cabinet
	U Height	8U
	Special Features	Adjustable Mounting Rails
	Special Features	Lockable Top Hatch
	Special Features	Wall-Mountable
	Special Features	Ships Fully Assembled
	Mounting Rail Profile	C-Shape
	Fan Options	Two Optional Fans: 120 mm
	Mounting Hole Types	Threaded Hole
	Industry Standards	EIA/ECA-310-E
<b>Performance</b>	Weight Capacity	198.9 lb [90 kg]
<b>Physical Characteristics</b>	Color	Black
	Front Door Construction	Steel
	Front Door Features	Secure Key Lock with Reversible and Removable Front Door
	Side Panel Construction	Steel
<b>Product Measurements</b>	Internal Width	25.3 in [6.4 cm]
	Internal Depth	14.8 in [3.8 cm]
	Product Length	15.1 in [3.8 cm]

Product Width	25.4 in [6.4 cm]
Product Height	37.0 in [9.4 cm]
Weight of Product	80.7 lb [36.5 kg]
Maximum Mounting Depth	29.9 in [7.6 cm]

---

<b>Packaging Information</b>	Flat Pack (Assembly Required)	No
	Package Length	18.1 in [4.6 cm]
	Package Width	28.3 in [7.2 cm]
	Package Height	3.3 ft [1.0 m]
	Shipping (Package) Weight	86.2 lb [39 kg]

---

<b>What's in the Box</b>	Included in Package	wall-mount rack
	Included in Package	door keys
	Included in Package	front-panel keys
	Included in Package	12-24 screws
	Included in Package	plastic washers
	Included in Package	instruction manual

---

***\*Product appearance and specifications are subject to change without notice.***

