

2-Post 9U Heavy-Duty Wall-Mount Network Rack, 19" Open Frame Server Rack, 18" Deep, Wall Mount Data Rack for IT / AV / Patch Panel / Computer Equipment

Product ID: RK919WALLO



This open-frame 9u wall mount rack provides 9U of storage, allowing you to save space and stay organized. The 19 inch equipment rack can hold up to 175 lb. (80 kg).

The wall mount open-frame rack is 18 in. (45.7 cm) deep, so it's perfect for smaller spaces. It ships fully assembled and features mounting holes that are spaced 16 in. apart, making it suitable for mounting on almost any wall, based on common wall-frame stud spacing.

You can mount the wall mount open-frame rack where space is limited, such as on a server room wall, office, or above a doorway, to expand your workspace and ensure your equipment is easy to access.

By having an open frame, the small wall mount network rack provides passive cooling to equipment. Additionally, the open frame provides easy access and the ability to configure your equipment, allowing you to maximize productivity.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

The RJ919WALLO is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization
- Mounting audio video broadcast or distribution components

Features

- **2-POST 9U WALL MOUNT NETWORK RACK:** EIA/ECA-310 compliant open frame server rack with 17.1" (43.5cm) mounting depth is ideal for installing IT / AV / Data equipment, patch panels, switches and shelves in small spaces
- **HEAVY DUTY:** This heavy duty 2 post open frame rack supports unobstructed airflow and is easy to install with a durable design made from SPCC cold-rolled steel with support for up to 176lbs (80Kg) of equipment
- **FULLY ASSEMBLED:** The IT server rack ships fully assembled with all of the rack screws and cage nuts required to mount your equipment; Wall Mount Data Rack is EIA/ECA-310-E Compliant
- **HARDWARE INCLUDED:** The 2 post open frame wall mount server rack includes a complete set of M6 square cage nuts, M6 screws, and hook and loop to securely mount all of your equipment in the rack
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 9U open frame wall mount rack is backed for 5 years, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	9U
Special Features	Easy Assembly
	Wall-Mountable
Mounting Rail Profile	G-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	176.4 lb [80 kg]
-----------------	------------------

Special Notes / Requirements

Note	Please Note: Maximum mounting depth does not account for the space needed for cabling
------	---

Physical Characteristics

Color	Black
Construction Material	Steel

Product Measurements

Product Length	18.0 in [45.7 cm]
Product Width	21.9 in [55.5 cm]
Product Height	21.3 in [54.0 cm]
Weight of Product	21.8 lb [9.9 kg]
Maximum Mounting Depth	17.1 in [43.5 cm]

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	24.4 in [62.0 cm]
Package Width	21.0 in [53.3 cm]
Package Height	24.4 in [62.0 cm]
Shipping (Package) Weight	27.6 lb [12.5 kg]

What's in the Box

Included in Package	1 - Rack
	24 - M6 Screws
	24 - M6 Nuts
	1 - 10 Foot Length of Black Hook and Loop

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***