

## 9U Wall-Mount Server Rack Cabinet - Up to 19 in. Deep

**Product ID:** RK920WALM



This 9U server or network rack cabinet lets you mount your EIA-310 compliant equipment to the wall, in a secure enclosure. The enclosure features adjustable mounting depth from 2 to 19 in. to provide a robust storage solution for your rack-mount equipment.

To provide secure stability for your heaviest equipment, this rack offers 4-post mounting, supporting a higher weight capacity per U than 2-post racks and supporting a total load capacity of up to 200 lb. (90 kg).

Save valuable floor space, by wall-mounting the enclosure. The wall-mounted design makes this enclosure the ideal solution for optimizing equipment storage in your classroom, retail store, server room or office. This rack also includes a 1U shelf that gives you a stable surface for storing your tools placing equipment that's not rack-mountable.

The wall-mount network rack makes it easy to install your equipment, with cage nuts and mounting screws included. The rack includes all of the hardware you need to mount your equipment in the rack, saving you the time, hassle and cost of sourcing mounting hardware. The 9U network cabinet features a removable and reversible front door and removable side panels, each with quick-release mechanisms, so you can easily access your equipment. Plus, each door and panel on this rack features an independent lock, ensuring your equipment is secure.

For hassle-free cable management, the rack includes a 3-meter roll of hook-and-loop cable tie that makes it easy to keep your cables neat and tidy by binding them together or binding them to the rack. The self-gripping fabric can be cut to any size, enabling a wrap-around solution for the cables of any rack-mount equipment.

This server rack enclosure features heavy-duty steel construction, with lockable doors at all entrances. For hassle-free equipment installation, the mounting rails on the rack can be switched for use with square holes and cage nuts, or tapped rails.

To ensure your equipment is running at an optimal temperature, the server rack/cabinet promotes passive cooling. It features mesh doors and vented top and bottom panels for maximum airflow.

For simple and sturdy mounting, the rack's mounting holes are positioned 16 in. apart, so you can securely attach it to a wall using wall studs.

The RK920WALM is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Wall-mount your server and networking equipment flush against the wall, in areas with limited space, such as technology store fronts or repair centers
- Install the rack in your small office environment, where you can't fit a full-sized rack
- Organize cabling or equipment in your network closet, wiring closet, back office or IDF

### Features

- Save space by wall-mounting your servers or networking equipment
- Easily install your equipment with mounting hardware included
- Secure your mission-critical equipment with a locked enclosure
- Maximize compatibility by switching the mounting rails between square cage nut holes or tapped 12-24 holes
- 1U shelf and hook-and-loop cable tie included

---

#### Hardware

|                  |  |
|------------------|--|
| Warranty         | 5 Years                                |
| Wallmountable    | Yes                                    |
| Rack Type        | 4-Post                                 |
| Frame Type       | Enclosed Cabinet                       |
| U Height         | 9U                                     |
| Special Features | Adjustable Mounting Rails              |
|                  | Built-in Cable Management              |
|                  | Grounding Lug(s)                       |
|                  | U-Markings                             |
|                  | Wall-Mountable with Rear Access Hinges |
|                  | Ships Fully Assembled                  |



|                       |  |
|-----------------------|--|
| Mounting Rail Profile | L-Shape                                |
| Fan Options           | Four Optional Fans: 120 mm             |
| Mounting Hole Types   | Square (For Cage Nut)<br>Threaded Hole |
| Industry Standards    | EIA/ECA-310-E                          |

---

#### Performance

|                 |                  |
|-----------------|------------------|
| Weight Capacity | 198.9 lb [90 kg] |
|-----------------|------------------|

---

#### Special Notes / Requirements

|      |  |
|------|--|
| Note | Includes CABSHELFV1U and 2 pairs of keys |
|------|--|

---

#### Physical Characteristics

|                         |  |
|-------------------------|--|
| Color                   | Black  |
| Front Door Construction | Steel Mesh   |
| Front Door Features     | Secure Key Lock with Reversible and Removable Front Door |
| Side Panel Construction | Steel Mesh   |
| Side Panel Features     | Secure Key Lock with Removable Side Panels               |

---

#### Product Measurements

|                        |                   |
|------------------------|-------------------|
| Internal Width         | 23.7 in [60.2 cm] |
| Internal Depth         | 21.5 in [54.7 cm] |
| Product Length         | 21.7 in [55.1 cm] |
| Product Width          | 23.7 in [60.2 cm] |
| Product Height         | 19.9 in [50.5 cm] |
| Weight of Product      | 46.4 lb [21.0 kg] |
| Maximum Mounting Depth | 18.9 in [48 cm]   |
| Minimum Mounting Depth | 2.4 in [60 mm]    |

---

**Packaging Information**

|                               |                   |
|-------------------------------|-------------------|
| Flat Pack (Assembly Required) | No                |
| Package Length                | 25.0 in [63.5 cm] |
| Package Width                 | 26.6 in [67.5 cm] |
| Package Height                | 23.2 in [59 cm]   |
| Shipping (Package) Weight     | 48.6 lb [22.0 kg] |

---

**What's in the Box**

|                     |                                |
|---------------------|--------------------------------|
| Included in Package | wall-mount enclosure           |
|                     | 1U shelf                       |
|                     | roll of hook-and-loop fastener |
|                     | 12-24 cage nuts                |
|                     | 12-24 screws                   |
|                     | door keys                      |
|                     | side panel keys                |
|                     | instruction manual             |

---

***\*Product appearance and specifications are subject to change without notice.***

