

Refurbished 1U 15" Rackmount LCD Console - USB + PS/2

Product ID: RKCONS1501R



The 1U LCD Rack Console by StarTech.com is a 19" wide drawer designed for applications where cabinet space is at a premium. The RKCONS1501R offers a single port KVM integrated module, has an eye-catching 15-inch active-matrix LCD monitor, full size 106-key keyboard (QWERTY), and a mouse touchpad. When the RKCONS1501R is not in use, you can close the console like a laptop and slide it into the cabinet and out of your way.

The LCD Rack Console is able to work with virtually any existing KVM switch and any standard rack or cabinet that is 30" or greater in depth. All refurbished RACKCONS LCD Consoles have been individually tested by StarTech.com technicians and are guaranteed to be fully functional. Units include complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the black paint on the metal casing, but all other components are as new. Every refurbished RACKCONS LCD Console is backed by a 90-day replacement warranty, plus free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Centralized control of dozens of PCs and servers if used with optional KVM

- Improving the internal space efficiency of existing cabinets
- Managing cabinet mounted servers

Features

- Bright Active Matrix TFT Display
- Durable design
- OSD function (On Screen Display) for LCD display
- Security features, including port locking and auto scan

Hardware

Warranty	None
Front Door Key Lock	Yes
Audio	No
Display Size	15in
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	PS/2
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	Yes
Daisy-Chain	Yes

Performance

On-Screen Display	Yes
IP Control	No
Maximum Analog Resolutions	Up to 1280 x 1024 @ 85Hz
Aspect Ratio	Standard (4:3)
Response Time	8ms

Contrast Ratio	400:1
Brightness	250 cd/m
Color Depth	32-bit
Pixel Pitch Support	0.297 x 0.297 mm
Viewing Angle	160 (H), 130 (V)
Maximum Number of Users	1
Port Selection Support	Hotkeys and OSD (On Screen Display)

Connector(s)

Host Connectors	2 - PS/2 (6 pin, Mini-DIN)
	1 - VGA (15 pin, High Density D-Sub)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Power

Power Source	AC Adapter Included
Input Voltage	115V-230V AC

Environmental

Operating Temperature	0 ~ 50 C / 32 ~ 122 F
Storage Temperature	20 ~ 60 C / -4 ~ 140 F

Physical Characteristics

Color	Black
Material	Heavy Duty Steel
Product Length	20.9 in [53.0 cm]
Product Width	18.9 in [48.1 cm]
Product Height	1.8 in [4.5 cm]
Weight of Product	24.3 lb [11.0 kg]

Maximum Mounting Depth 31.5 in [80 cm]

Minimum Mounting Depth 21.7 in [55 cm]

Packaging Information

Package Length	22.4 in [56.8 cm]
Package Width	26.2 in [66.5 cm]
Package Height	8.3 in [21.0 cm]
Shipping (Package) Weight	36.6 lb [16.6 kg]

What's in the Box

Included in Package	1 - 1U LCD Rack Console Drawer (1)
	1 - Mounting Rails - Set (1)
	1 - Console Cable Kit (1)
	1 - Power Adapter (1)

Warranty Information

Warranty	Refurbished 90 Days
----------	---------------------

****Product appearance and specifications are subject to change without notice.***