

1U 17" Rackmount LCD Console - USB + PS/2

Product ID: RKCONS1701GB



The RKCONS1701GB 1U 17" Rack Mount LCD Console provides a complete keyboard, video and mouse control point, integrated neatly into only 1U of rack/cabinet space - providing complete KVM control right from a server rack.

Offering a durable, compactable 1U design, when the rack console is not in use it's as simple as folding the display like a laptop computer, and sliding it back into the server rack on the sturdy mounting rails (included). The included key lock provides an added security layer, helping to reduce unauthorized access to connected computers.

Offering consolidated control from a convenient location, the KVM rack console can be connected to virtually any multiport KVM switch, for control of multiple servers/computers, providing a scalable KVM control solution that lets you determine the type of KVM switch to use based on function and budget.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Centralized control of dozens of PCs and servers if used with optional KVM

- Managing cabinet mounted servers
- Improving the internal space efficiency of existing cabinets

Features

- Bright Active Matrix TFT Display
- Durable design
- OSD function (On Screen Display) for LCD display
- Security features, including port locking and auto scan
- Supports both USB and PS/2 connected servers or KVMs

Hardware

| | |
|------------------------------|-----------------------|
| Warranty | 2 Years |
| Front Door Key Lock | Yes |
| Audio | No |
| Display Size | 17in |
| Panel Type | Active Matrix TFT LCD |
| KVM Ports | 1 |
| PC Interface | USB and PS/2 |
| PC Video Type | VGA |
| Number of Monitors Supported | 1 |
| Rack-Mountable | Yes |

Performance

| | |
|----------------------------|----------------|
| On-Screen Display | Yes |
| IP Control | No |
| Maximum Analog Resolutions | 1280X1024 |
| Aspect Ratio | Standard (4:3) |
| Response Time | 5ms |

| | |
|------------------------|-------------------------------------|
| Contrast Ratio | 1000:1 |
| Brightness | 250 cd/m |
| Pixel Pitch Support | 0.264 x 0.264 mm |
| Viewing Angle | 170 (H), 160 (V) |
| Sync | 45~80KHZ |
| Port Selection Support | Hotkeys and OSD (On Screen Display) |

Connector(s)

| | |
|----------------------|--------------------------------------|
| Console Interface(s) | 2 - PS/2 (6 pin, Mini-DIN) |
| | 1 - USB 2.0 Type-A (4 pin, 480Mbps) |
| | 1 - VGA (15 pin, High Density D-Sub) |

Software

| | |
|------------------|---|
| OS Compatibility | OS independent; No software or drivers required |
|------------------|---|

Power

| | |
|------------------------------|---------------------|
| Power Source | AC Adapter Included |
| Output Voltage | 12V DC |
| Output Current | 4A |
| Center Tip Polarity | Positive |
| Power Consumption (In Watts) | 25 |

Environmental

| | |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 50C (32F to 122F) |
| Storage Temperature | -20C to 60C (-4F to 140F) |

Physical Characteristics

| | |
|--------------|-------------------------------|
| Color | Black |
| Material | Heavy Duty Steel |
| Cable Length | 6ft (1.83m) Console Cable Kit |

| | |
|------------------------|-------------------|
| Product Length | 20.9 in [53.0 cm] |
| Product Width | 18.9 in [48.1 cm] |
| Product Height | 1.8 in [4.5 cm] |
| Weight of Product | 26.5 lb [12.0 kg] |
| Maximum Mounting Depth | 31.5 in [80 cm] |
| Minimum Mounting Depth | 21.7 in [55 cm] |

Packaging Information

| | |
|---------------------------|-------------------|
| Package Quantity | 1 |
| Package Length | 22.4 in [56.8 cm] |
| Package Width | 26.2 in [66.5 cm] |
| Package Height | 8.3 in [21.0 cm] |
| Shipping (Package) Weight | 38.0 lb [17.2 kg] |

What's in the Box

| | |
|---------------------|------------------------------------|
| Included in Package | 1 - 1U LCD Rack Console Drawer (1) |
| | 1 - Mounting Rails - Set (1) |
| | 1 - Console Cable Kit (1) |
| | 1 - Power Adapter (1) |

Warranty Information

| | |
|----------|---------|
| Warranty | 2 Years |
|----------|---------|

****Product appearance and specifications are subject to change without notice.***