

Refurbished DuraView 17" Folding LCD Rack Console with 8 Port Multi-Platform KVM

Product ID: RKCONS1708R



Refurbished units may have minor scratches or dents.

The 1U LCD Rack Console by StarTech.com is a 19" wide drawer designed for applications where cabinet space is at a premium. The RKCONS1708R offers an 8 Port KVM module, has an eye-catching 17-inch active-matrix LCD monitor, full size 106-key keyboard, and a mouse touchpad. When the RKCONS1708R is not in use, you can close the console like a laptop and slide it into the cabinet and out of your way.

The LCD Rack Console is able to work with virtually any existing KVM switch and any standard rack or cabinet that is 30" or greater in depth. The product is capable of managing up to 64 servers through eight cascaded 8-port KVMs. All refurbished RACKCONS LCD Consoles have been individually tested by StarTech.com technicians and are guaranteed to be fully functional. Units include complete mounting hardware and accessories as intended with the original (non-refurbished) product, and are provided in the original packaging. Refurbished units may have small scratches in the black paint on the metal casing, but all other components are as new. Every refurbished RACKCONS LCD Console is backed by a 90-day replacement warranty, plus free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Centralized control of up to 64 PCs
- Improving the internal space efficiency of existing cabinets
- Managing cabinet mounted servers
- User can complete the basic tasks in the server room

Features

- Auto Scan Mode lets you switch between computers for easy monitoring
- Cascadable design
- Compatible with PC, Mac and Sun servers and systems
- Durable design
- Hot-pluggable
- Login authentication restricts access to authorized users
- On Screen Display (OSD)
- Security features, including port locking and auto scan
- Supports PCs with USB or PS/2 keyboard and mouse connectors
- Universal 8 port KVM switch Module controls up to 8 computers directly and up to 64 computers by cascading 8 additional KVM switches

Hardware

Warranty	None
Front Door Key Lock	Yes
Audio	No
Display Size	17in
Panel Type	Active Matrix TFT LCD
KVM Ports	8
PC Interface	USB and PS/2
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	Yes
Daisy-Chain	Yes

Performance

On-Screen Display	Yes
IP Control	No



Maximum Analog Resolutions	1280x1024 @85Hz (SXGA)
Aspect Ratio	Standard (4:3)
Response Time	5ms
Contrast Ratio	1000:1
Brightness	250 cd/m
Color Depth	32-bit
Pixel Pitch Support	0.264 x 0.264 mm
Viewing Angle	170 (H), 160 (V)
Maximum Number of Users	1
Maximum Cascaded Computers	64
Port Selection Support	Hotkeys and OSD (On Screen Display)

Connector(s)

Console Interface(s)	Centronics (36 pin) PS/2 (6 pin, Mini-DIN) VGA (15 pin, High Density D-Sub)
Host Connectors	VGA (15 pin, High Density D-Sub)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Power

Power Source	AC Adapter Included
Input Voltage	115V-230V AC
Output Voltage	12V DC
Output Current	4A
Center Tip Polarity	Positive

Environmental



Operating Temperature	0 – 50 C / 32 – 122 F
Storage Temperature	-20 – 60 C / -4 -140 F
Humidity	10%~90%RH

Physical Characteristics

Color	Black
Material	Heavy Duty Steel
Product Length	18.5 in [47 cm]
Product Width	17.3 in [44 cm]
Product Height	1.7 in [44 mm]
Weight of Product	24.3 lb [11 kg]
Minimum Mounting Depth	30.0 in [76.2 cm]

Packaging Information

Package Length	22.4 in [56.8 cm]
Package Width	30.7 in [78 cm]
Package Height	8.3 in [21.1 cm]
Shipping (Package) Weight	44.5 lb [20.1 kg]

What's in the Box

Included in Package	1U 8 Port Multi-Platform KVM Switch
	1U LCD Rack Console Drawer
	Mounting Rails (Set)
	Power Adapter

****Product appearance and specifications are subject to change without notice.***

