

## 16 Port Rackmount KVM Console w/ 6ft Cables - Integrated KVM Switch w/ 17" LCD Monitor - Fully Featured 1U LCD KVM Drawer- OSD KVM - Durable 50,000 MTBF - USB + VGA Support

Product ID: RKCONS1716K



Providing centralized control of up to 16 servers, this 16-port rackmount KVM console gives you easy access to your systems. With a minimal footprint, it mounts in a server rack or cabinet using only 1U of rackspace.

The 1U rackmount console features a built-in keyboard, and a touchpad for intuitive control, as well as a 17-inch LCD display that supports resolutions up to 1280x1024.

This 16-port KVM console comes with everything you need to set upright out of the box: 

- 16 VGA KVM Cables
- Mounting Rails
- M5 Cage Nuts and Screws

With direct access to 16 systems or servers, the 16-port KVM module gives you the flexibility you need to easily integrate the console into your existing server infrastructure.

Rack consoles provide convenient, rack-mounted control options for single servers or the entire server room. KVM consoles include LCD display, keyboard, and trackpad, all sliding into 1U of rack space. The RKCONS1716K is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Control up to 16 systems directly from the console, or dozens of KVM-connected computers
- Manage cabinet-mounted servers and KVM switches

### Features

- **TECH SPECIFICATIONS:** Rackmount KVM Console, 17" Active Matrix TFT LCD Monitor, 1280 x 1024, 16 port VGA KVM switch w/ 6 ft. cables, 99 key full keyboard + numeric keypad & trackpad; Supports USB 2.0
- **PROFESSIONAL & SECURE:** Customizable hot-keys, on-screen display (OSD), multi-level user security, user access levels / port permissions, & auto scan
- **INTEGRATED DESIGN:** Combines a KVM + Console w/ integrated power supply into 1U of rack space allowing space for other equipment. Mount depth: 23.8" [60.5 cm] to 35" [89 cm] (incl. mounting hardware)
- **HEAVY DUTY:** LCD KVM drawer has durable steel construction and heavy duty rail design that supports frequent use in operating environments from 0C to 40C (32F to 104F) with an MTBF of 50,000 hours
- **TESTED & PROVEN:** This OS independent rack console is universally compatible w/ leading servers and backed by a StarTech.com 2-year warranty and free lifetime 24/5 multilingual technical support

<b>Hardware</b>	Warranty	2 Years
	U Height	1U
	Front Door Key Lock	No
	Audio	No
	Display Size	17in
	Panel Type	Active Matrix TFT LCD
	KVM Ports	16
	PC Interface	USB
	PC Video Type	VGA
	Number of Monitors Supported	1
	Rack-Mountable	Yes
	Cables Included	Yes
	Daisy-Chain	No
	<b>Performance</b>	On-Screen Display
IP Control		No
Hot-Key Selection		Yes
Maximum Analog Resolutions		1280 x 1024
Supported Resolutions		Resolutions up to 1280 x 1024 @ 60Hz
Aspect Ratio		5:4
Response Time		5ms
Contrast Ratio		1000:1
Brightness		250 cd/m
Color Depth		8-bit, 16.7M colors
		0.264 x 0.264 mm

Pixel Pitch Support	170 (H), 160 (V)
Viewing Angle	1
Maximum Number of Users	Push Button, Hotkeys, and OSD (On Screen Display)
Port Selection Support	50, 000 Hrs
MTBF	

---

<b>Connector(s)</b>	Console Interface(s)	VGA (15 pin, High Density D-Sub)
	Console Interface(s)	USB Type-A (4 pin) USB 2.0
	Host Connectors	VGA (15 pin, High Density D-Sub)
	Other Interface(s)	15 Pin High Density D-Sub

---

<b>Special Notes / Requirements</b>	Note	The minimum mounting depth of this rackmount console is less than the length of the console itself. Please consider the length of the rackmount console when evaluating if it will fit into your rack.
-------------------------------------	------	--

---

<b>Indicators</b>	LED Indicators	Green/Red - Online/Selected LED
-------------------	----------------	---------------------------------

---

<b>Power</b>	Power Source	International Power Cords
	Input Voltage	100 - 240 AC
	Input Current	1.5A
	Power Consumption (In Watts)	23W

---

<b>Environmental</b>	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	10 ~ 80% RH

---

<b>Physical Characteristics</b>	Color	Black
	Material	Steel
	Cable Length	6 ft
	Product Length	22.9 in [5.8 cm]
	Product Width	17.6 in [4.5 cm]
	Product Height	1.7 in [42.500 mm]
	Weight of Product	30.3 lb [13.7 kg]
	Maximum Mounting Depth	35.4 in [9 cm]

Minimum Mounting Depth 22.0 in [5.6 cm]

---

<b>Packaging Information</b>	Package Length	30.1 in [7.6 cm]
	Package Width	24.2 in [6.2 cm]
	Package Height	7.3 in [1.8 cm]
	Shipping (Package) Weight	46.4 lb [21.0 kg]

---

<b>What's in the Box</b>	Included in Package	KVM Console
	Included in Package	Mounting Rails
	Included in Package	5.9 ft [1.8 m] KVM Cables
	Included in Package	M5 Cage Nuts
	Included in Package	M5 Screws
	Included in Package	5.9 ft [1.8 m] Regional Power Cords (NA, JP, UK, EU, ANZ)
	Included in Package	Quick-Start Guide

---

***\*Product appearance and specifications are subject to change without notice.***

