

1U 19" Rackmount LCD Console - USB + PS/2

Product ID: RKCONS1901EU



The RKCONS1901EU 1U 19" Rack Mount LCD Console provides a complete keyboard, video and mouse control point, integrated neatly into only 1U of rack/cabinet space - providing complete KVM control right from a server rack.

Offering a durable, compactable 1U design, when the rack console is not in use it's as simple as folding the display like a laptop computer, and sliding it back into the server rack on the sturdy mounting rails (included). The included key lock provides an added security layer, helping to reduce unauthorized access to connected computers.

Offering consolidated control from a convenient location, the KVM rack console can be connected to virtually any multiport KVM switch, for control of multiple servers/computers, providing a scalable KVM control solution that lets you determine the type of KVM switch to use based on function and budget.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Centralized control of dozens of PCs and servers if used with optional KVM
- Improving the internal space efficiency of existing cabinets
- Managing cabinet mounted servers

Features

- Bright 19" Active Matrix TFT Display

- VGA video input support
- Compatible with USB or PS/2 PCs and KVMs
- Durable 1U rack-mountable design
- OSD function (On Screen Display) for LCD display
- Security features, including port locking and auto scan

Hardware

Warranty	2 Years
Front Door Key Lock	Yes
Audio	No
Display Size	19"
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	USB and PS/2
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	Yes

Performance

On-Screen Display	Yes
IP Control	No
Maximum Analog Resolutions	1280x1024(SXGA)@60Hz
Aspect Ratio	4:3
Response Time	5ms
Contrast Ratio	500:1
Brightness	250 cd/m
Color Depth	24-bit, 16.7M colors (Truecolor)



Pixel Pitch Support	0.294 x 0.294 mm
Viewing Angle	176 (H), 170 (V)
Maximum Number of Users	1
Port Selection Support	Hotkeys and OSD (On Screen Display)
MTBF	60,000 Hours

Connector(s)

Host Connectors	VGA (15 pin, High Density D-Sub) PS/2 (6 pin, Mini-DIN) USB Type-A (4 pin) USB 2.0
-----------------	--

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Power

Power Source	International Power Cords
Input Voltage	100 - 240 AC
Power Consumption (In Watts)	48

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)

Physical Characteristics

Color	Black
Material	Heavy Duty Steel
Product Length	22.6 in [57.5 cm]
Product Width	18.9 in [48 cm]
Product Height	1.8 in [45 mm]
Weight of Product	30.3 lb [13.7 kg]



Maximum Mounting Depth 31.5 in [80 cm]

Minimum Mounting Depth 21.9 in [55.5 cm]

Packaging Information

Package Length 22.4 in [56.8 cm]

Package Width 28.1 in [71.4 cm]

Package Height 8.3 in [21 cm]

Shipping (Package) Weight 43.1 lb [19.5 kg]

What's in the Box

Included in Package 1U LCD Rack Console Drawer

Mounting Rails - Set

Console Cable Kit

Power Cord

Set of Keys

Set of Mounting Screws

User Manual

Manual on CD

****Product appearance and specifications are subject to change without notice.***

