

1U 20" High Resolution Folding Rackmount LCD Console for 19in Rack

Product ID: RKCONS2001GB



The RKCONS2001GB 1U 20-inch High Resolution Folding Rack Mount LCD Console (for 19-inch racks) provides total KVM control right from your server rack, with a complete keyboard, monitor, mouse, and audio control point integrated into a space-efficient 1U of rack/cabinet space.

This durable and compact KVM Rack Console offers the largest (20.1-inches) and highest resolution (up to 1600x1200) TFT-LCD monitor available in a 1U rackmount design. When not in use, it can be folded and slid back into the server rack on sturdy mounting rails (included).

With the included cables, the LCD console can be connected to virtually any multi-port KVM switch for control of multiple servers/computers, providing a scalable solution that lets you determine the type of KVM switch to use. Plus, the console supports connection to PS/2, USB, VGA and DVI systems, accommodating both legacy and cutting edge computers.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Rack mount LCD Console solution for server applications requiring high resolutions
- Centralized control of dozens of PCs and servers if used with optional KVM
- Improving the internal space efficiency of existing cabinets
- Managing cabinet mounted servers and KVM switches

Features


- High resolution 20.1" LCD display
- VGA and DVI video input support
- Compatible with both USB and PS/2 PCs and KVMs
- USB 2.0 pass through port on front of unit
- Built-in speakers
- OSD menu (On Screen Display) for LCD display functions
- Lockable LCD display for security
- Tempered glass LCD panel
- Durable, heavy duty steel design
- English (UK - British) spec keyboard
- Bright Active Matrix TFT Display

Hardware

Warranty	2 Years
U Height	1U
Front Door Key Lock	Yes
Audio	No
Display Size	20in
Panel Type	Active Matrix TFT LCD
KVM Ports	1
PC Interface	USB and PS/2
PC Video Type	DVI+VGA
Number of Monitors Supported	1
Rack-Mountable	Yes

Performance

IP Control	No
------------	----



Maximum Analog Resolutions	1600 x 1200 (UXGA)
Aspect Ratio	Standard (4:3)
Response Time	16ms
Contrast Ratio	700:1
Brightness	300 cd/m
Color Depth	24-bit, 16.7M colors (Truecolor)
Pixel Pitch Support	0.255 x 0.255 mm
Viewing Angle	178 (H), 178 (V)
Maximum Number of Users	1
MTBF	60,000 Hours

Connector(s)

Host Connectors	3.5 mm Mini-Jack (3 Position) DVI-I (29 pin) PS/2 (6 pin, Mini-DIN) USB Type-A (4 pin) USB 2.0 VGA (15 pin, High Density D-Sub)
-----------------	---

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Power

Power Source	AC Adapter Included
Input Voltage	110V-240V AC
Output Voltage	18 DC
Output Current	3.3A
Center Tip Polarity	Positive
Plug Type	N



Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	10~90% RH

Physical Characteristics

Color	Black
Material	Heavy Duty Steel
Product Length	24.0 in [60.8 cm]
Product Width	17.7 in [44.9 cm]
Product Height	1.7 in [44 mm]
Weight of Product	34.3 lb [15.5 kg]
Maximum Mounting Depth	39.4 in [100 cm]
Minimum Mounting Depth	30.1 in [76.4 cm]

Packaging Information

Package Length	21.7 in [55 cm]
Package Width	31.7 in [80.6 cm]
Package Height	7.9 in [20 cm]
Shipping (Package) Weight	47.1 lb [21.3 kg]

What's in the Box

Included in Package	1U 20.1in LCD Rack Console Drawer
	Mounting Rails - Set
	3.5mm Audio cable
	6 ft DVI Cable
	6 ft USB A to A Male Male cables
	PS2 and VGA Console cable



Set of Keys

Set of mounting screws

Power Cord

Power Adapter

User Manual

****Product appearance and specifications are subject to change without notice.***

