


4U Universal VESA LCD Monitor Mounting Bracket for 19-inch Rack or Cabinet - TAA Compliant - Cold-Pressed Steel Bracket

Produkt ID: RKLcdbk



The RKLcdbk Universal VESA LCD Monitor Mounting Bracket for 19in Rack or Cabinet lets you mount almost any retail LCD or Touch screen panel into a server/storage rack/cabinet. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The LCD mounting bracket is made of solid cold pressed steel (SPCC), is designed to support 100mm and 75mm VESA mounted LCD panels, and meets ANSI/EIA RS-310-D standards rack mounting. A unique adjustable design enables an LCD panel to be mounted into the cabinet at various depths - allowing the rack/cabinet door to be closed.

The LCD mounting bracket also supports wall-mounted LCD installation, by inverting the adjustable bracket or by adding this bracket to a wall mount bracket or rack, such as the 6U (10 inch) Wallmount Bracket for 19" Rack Equipment (WALLMOUNT6) or 8U Open Frame Wall Mount Equipment Rack (RK812WALLO).

Backed by a StarTech.com Lifetime warranty.

Certifikat, rapporter och kompatibilitet



Användning

- Ideal for installing a retail LCD monitor into an existing Rack or Cabinet solution
- Use for uptime/process monitoring with big screens over 19" when mounted outwards
- Adding a monitoring display to a security rack or cabinet
- Installing a touch screen display into a rack or cabinet
- Mounting an LCD monitor or TV to the wall

Funktioner

- **STURDY DESIGN:** The LCD mounting bracket made of solid cold pressed steel (SPCC), is designed to support 100mm & 75mm VESA mounted LCD panels, and meets ANSI/EIA RS-310-D standards rack mounting
- **ADJUSTABLE DEPTH:** A unique adjustable design enables an LCD panel to be mounted into the AV rack cabinet at various depths, allowing the rack/cabinet door to be closed
- **ADDED FUNCTIONALITY:** The rackmount monitor bracket supports wall-mounted LCD installations by inverting or adding this bracket to a wall mount bracket or rack, such as the 6U Wall mount Bracket
- **TAA COMPLIANT:** This TAA compliant Universal VESA LCD Monitor Mounting Bracket adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this LCD mounting bracket is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hårdvara

Garantipolicy	Lifetime
Ramtyp	Stål
U-höjd	4U
Kabelhantering	Nej
Industristandarder	EIA RS310-D

Utseende

Färg	Svart
Kabinetttyp	Stål

Inre bredd	17.3 in [43.9 cm]
Produktlängd	4.5 in [11.3 cm]
Produktbredd	19.0 in [48.3 cm]
Produkthöjd	7.0 in [17.8 cm]
Produktvikt	3.6 lb [1.7 kg]
Maximalt monteringsdjup	3.5 in [8.9 cm]
Minsta monteringsdjup	0.0 in [0 cm]

Förpackning

Förpackningsantal	1
Paketets längd	7.9 in [20.1 cm]
Package Width	18.5 in [46.9 cm]
Paketets höjd	2.1 in [5.3 cm]
Fraktvikt (förpackning)	4.2 lb [1.9 kg]

Vad det är i lådan

Ingår i paketet	2 - mounting brackets
	1 - LCD bracket
	8 - M5 cage nuts
	8 - M5 screws
	4 - M4 x 10mm LCD mounting screws
	4 - M5 x 10mm bracket screws
	4 - washers
	1 - instruction manual

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.